



## RL-5250 | INDUSTRIAL 360° LED LANTERN

- 5250 lumen 50W 160 x SMD LEDs, 6500k
- Dual Power - rechargeable battery and mains powered
- 360° and 180° Lighting modes
- Ultra tough nylon polymer construction
- Milky polycarbonate diffuser for even light dispersion
- Stainless steel carry handle on the top
- Concealed ultra tough hanging hook in the base
- Screw hole in the base for attaching to tripods
- IP65 dust & water proof
- IK07 shock resistant
- High power 11.1v 5200mAh Li-ion battery
- Battery level and charging indicators
- Mains 15V 1.5A multi-country charger/power lead included
- Fast 3.5 hours charge time

**BATTERY** 11.1v 5200mAh Li-ion  
**WEIGHT** 1820g  
**DIMENSIONS** Ø157.5 x H 285.6 mm

**LUMEN** 5250LM | **RUNTIME** 2-16H | **BEAM** 44M | **IP RATING** IP65/IK07