

# PRODUCT DATASHEET

## SF CIRC 400 V 24W 830 IP44

SURFACE CIRCULAR 400 | Wall and ceiling luminaire with IP44



---

### Areas of application

- Corridors
- Stairways
- Bathrooms
- Foyers

---

### Product benefits

- High luminous efficacy
- Energy savings of up to 55 % compared to luminaires that use CFL
- Easy and quick installation
- Very homogenous light
- 3 years guarantee

---

### Product features

- Beam angle: 120°
- Type of protection: IP44 (ceiling mounting), IP20 (wall mounting)
- Impact resistance: IK03
- Metal housing, PMMA cover
- Ambient temperature in operation: -20...+40 °C


---

**TECHNICAL DATA****Electrical data**


Nominal wattage	24.00 W
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Nominal current	115 mA
Inrush current	7.3 A
Inrush current time $T_{h50}$	360 $\mu$ s
Max. no. of lum. on circuit break. B16 A	64
Max. no. of lum. on circuit break. C10 A	40
Max. no. of lum. on circuit break. C16 A	64
Power factor $\lambda$	> 0.55
Total harmonic distortion	< 120 %
Protection class	I
Operating mode	Integrated LED driver

**Photometrical data**

Luminous flux	1920 lm
Luminous efficacy	80 lm/W
Color temperature	3000 K
Light color (designation)	Warm white
Color rendering index Ra	> 80
Standard deviation of color matching	< 6 sdc <sub>m</sub>
Luminous intensity	-
Low flicker	Yes
Flickering metric (Pst LM)	-
Stroboscope effect metric (SVM)	-
Photobiological safety group acc. to EN62778	RG0
Photobiological safety group acc. to EN62471	RG0
Beam angle	120 °




LDC typ cone



LDC typ polar

**Dimensions & Weight**

Diameter	400.00 mm
Height	120.00 mm
Product weight	750.00 g



**Materials & Colors**

Product color	White
Housing color	White
Body material	Steel
Cover material	Polymethylmethacrylate (PMMA)

Light emitting surface material	PMMA
Glow Wire Test according to IEC 60695-2-12	650 °C
Mercury content	0.0 mg

### Application & Mounting

Ambient temperature range	-20...+40 °C
Temperature range at storage	-20...+80 °C
Type of connection	Terminal, 3-pin
Type of protection	IP44 <sup>1)</sup>
Protection class IK (shock resistance)	IK03
Dimmable	No
Mounting type	Surface
Mounting location	Ceiling / Wall
Application environment	Indoor
LED module replaceable	Not replaceable

<sup>1)</sup> Type of protection: IP44 (ceiling mounting), IP20 (wall mounting)

### Lifespan

Lifespan L70/B50 at 25 °C	30000 h
Lifespan L80/B10 at 25 °C	22000 h
Lifespan L90/B10 at 25 °C	15000 h
Number of switching cycles	50000

### Certificates & Standards

Standards	CE / CB / TÜV SÜD / EAC
Luminaire with limited surface temperature, "D sign"	No
Ball shot safe	No


### Additional product data

Product remark	Available from September 2021
----------------	-------------------------------












### EQUIPMENT / ACCESSORIES

– Replacement cover optional available

### DOWNLOAD DATA

DOWNLOAD DATA	
	User instruction SURFACE CIRCULAR SENSOR

**DOWNLOAD DATA**


	Addon Technical Information LS Insert SF Circular
	Addon Technical Information LS Insert SF Circular
	Tender documents Tender Text 4058075080058
	Tender documents SURFACE CIRCULAR 400 24W 830 IP44-EN
	Declarations of conformity
	Declarations of conformity SF CIRC
	IES file (IES) SF CIRC 400 V 24W 830 IP44
	LDT file (Eulumdat) SF CIRC 400 V 24W 830 IP44
	R3D file (Relux 3D Model) Surface circular 400
	M3D file (3D Model) Surface_Circular_400
	UGR file (UGR table) SF CIRC 400 V 24W 830 IP44

**LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075618022	Folding box 1	130 mm x 440 mm x 440 mm	912.00 g	25.17 dm <sup>3</sup>
4058075618039	Shipping box 5	665 mm x 455 mm x 460 mm	5866.00 g	139.18 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

**ADDITIONAL CATALOG INFORMATION**



**References / Links**

- For Guarantee see [www.ledvance.com/guarantee](http://www.ledvance.com/guarantee)

---

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.