

EL

Light Range Junction Boxes with Opaque Lids

Halogen free polystyrene junction boxes with screw down lids in RAL 7035.

Features and Benefits

- Includes supports for installation of DIN rail and mounting plates
- IK07



Junction Box with Opaque lid.

TYPE	Height mm	Width mm	Depth mm	IP Rating	Pack Cont.
EL111	108	108	64	IP67	1
EL161	162	116	78	IP67	1
EL171	175	151	95	IP67	1
EL231	241	180	95	IP67	1
EL322	328	239	129	IP67	1

i Versions with pre-moulded cable entries or transparent lids available on request

i Plastic and metal back plates also available on request

A

Adaptable Boxes with Opaque Lids

Plastic halogen free junction boxes with stepped glands and press-fit lids in RAL 7035


Features and Benefits

- Double insulated
- IK07
- Range of temperature -15°C to +60°C



Junction Box with Stepped Glands.

TYPE	Height mm	Width mm	Depth mm	Description	IP Rating	Pack Cont.
A165MM	65	-	35	Round	IP44	1
A280MM	80	-	35	Round	IP44	1
A3JB	80	80	40	Square	IP44	1



ASH

Adaptable Junction Boxes with Opaque Lids

Double insulated adaptable box with smooth walls and screw on lids in RAL 7035

Features and Benefits

- Double insulated
- IK08
- Installation temperature -15°C to +60°C



Junction Box with Opaque lid.

TYPE	Height mm	Width mm	Depth mm	IP Rating	Pack Cont.
ASH15	110	110	112	IP55	1
ASH25	150	110	150	IP55	1
ASH35	150	150	150	IP55	1
ASH45	220	150	150	IP55	1
ASH55	300	220	150	IP55	1

AS

Adaptable Junction Boxes with Opaque Lids

Plastic junction box with smooth walls and screw on lids in RAL 7035


Features and Benefits

- Double insulated
- IK08
- Installation temperature -15°C to +60°C



Junction Box Opaque lid.

TYPE	Height mm	Width mm	Depth mm	IP Rating	Pack Cont.
AS05	123	83	62	IP56	1
AS15	103	103	62	IP56	1
AS25	154	113	77	IP56	1
AS35	193	144	79	IP56	1
AS45	242	190	90	IP56	1
AS55	305	225	126	IP56	1
AS65	390	310	128	IP56	1



AS T

Adaptable Junction Boxes with Transparent Lids

Plastic adaptable box with smooth walls in RAL 7035 and screw on transparent lids

Features and Benefits

- Double insulated
- IK08
- Installation temperature -15°C to +60°C



Junction Box Transparent Lid.

TYPE	Height mm	Width mm	Depth mm	IP Rating	Pack Cont.
AS35T	190	140	70	IP56	1
AS45T	240	190	90	IP56	1
AS55T	300	220	150	IP56	1
AS65T	380	300	150	IP56	1

PB

Metal Mounting Plates for use with AS and ASH Junction Boxes

Metal mounting plates with cut outs for ease of installation



Metal Mounting Plate.

TYPE	For use with	Pack Cont.
PB1	AS35/AS35T	1
PB2	AS45/AS45T	1
PB3	AS55/AS55T	1
PB4	AS65/AS65T	1
PB5	ASH15/ASH15T	1
PB6	ASH25/ASH25T	1
PB7	ASH35/ASH35T	1
PB8	ASH45/ASH45T	1
PB9	ASH55/ASH55T	1