

Mini-Lynx Spiral

MLX SPIRAL T2 12W 827 E14 SLV
0031123



PRODUCT OVERVIEW

| | |
|----------------------------|-------------------------------|
| Product name | MLX SPIRAL T2 12W 827 E14 SLV |
| Technology | Compact Fluorescent |
| Watt (Rated) (W) | 12 |
| Lamp shape | Spiral |
| Type | Mini-Lynx Spiral |
| Cap/Base | E14 |
| Lamp finish | Frosted/Coated |
| E-number FI | 4940143 |
| Luminous flux (lm) | 630 |
| Colour temperature (K) | 2700 |
| Light colour | Homelight |
| CRI (Ra) | 80 |
| Wattage (W) | 12 |
| Average life (Nominal) (h) | 10000 |
| Product EAN number | 5410288311234 |

DATA TABLE

General data

| | |
|------------------|-------------------------------|
| Product name | MLX SPIRAL T2 12W 827 E14 SLV |
| Technology | Compact Fluorescent |
| Watt (Rated) (W) | 12 |
| Lamp shape | Spiral |
| Type | Mini-Lynx Spiral |
| Cap/Base | E14 |

Mini-Lynx Spiral

MLX SPIRAL T2 12W 827 E14 SLV
0031123

| | |
|-------------|----------------|
| Lamp finish | Frosted/Coated |
| E-number FI | 4940143 |

Optical data

| | |
|--|-----------|
| Luminous flux (lm) | 630 |
| Luminous flux (Rated) (lm) | 630 |
| Colour temperature (K) | 2700 |
| Light colour | Homelight |
| Colour Code | Hom |
| CRI (Ra) | 80 |
| Adjustable chromaticity | N |
| Lumen maintenance at end of nominal life (%) | 80 |

Electrical data

| | |
|---|--------|
| Wattage (W) | 12 |
| Equivalent watt (W) | 53 |
| Starting time (max) (s) | < 2 s |
| Warm-up time to 60% of full light (max) (s) | < 60 s |
| Mains voltage (V) | 230V~ |
| Lamp power factor | 0.5 |
| No. Of switching cycles before premature failures | >10000 |
| Transformer required | Yes |
| kWh per 1000 hours burning time | 12 |

Lifetime data

| | |
|----------------------------|-------|
| Average life (Nominal) (h) | 10000 |
| Average life (Rated) (h) | 10000 |

Physical data

| | |
|-----------------------------|-------|
| Max. Lamp Diameter (mm) - D | 46 |
| Weight (kg) | 0.019 |

Packaging

| | |
|---------------------------------------|----------------|
| Single packaging type | Carton |
| Product EAN number | 5410288311234 |
| Packaging single length / height (cm) | 4.8 |
| Packaging single width (cm) | 4.8 |
| Packaging single depth (cm) | 10.5 |
| DUN14 (inner) | 25410288311238 |
| Units per inner package | 10 |
| Packaging inner length / height (cm) | 30.0 |
| Packaging inner width (cm) | 14.1 |
| Packaging inner depth (cm) | 13.5 |
| DUN14 (outer) | 15410288311231 |
| Units per outer package | 50 |
| Packaging outer length / height (cm) | 74.5 |
| Packaging outer width (cm) | 32.0 |

Mini-Lynx Spiral

MLX SPIRAL T2 12W 827 E14 SLV
0031123

| | |
|-----------------------------------|------|
| Packaging outer depth (cm) | 16.5 |
|-----------------------------------|------|

Safety data

| | |
|---|------------|
| Lamp mercury content (mg) | 2.5 |
| Breakage cleaning instructions | Applicable |
| Recommendation for disposal at end of life | Applicable |
| Special purpose lamp | No |
| Dry applications use only | Yes |
| Suitable for household illumination | Yes |