



# CorePro GLASS LED candles and lustres

## CorePro LEDLusterND2-25W P45 E27 827 CLG

Featuring a classic heritage design, Classic filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lustres: compared to convential lamps, it provides a 90% energy saving. CorePro Glass LED candles and lustres provide excellent quality of light. By offering a lifetime of 15,000 hours, they reduce maintenance costs.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
Technical type	2-25W
	Sphere
Light Technical	
Colour Code	827 [ CCT of 2,700 K]
Luminous flux (nom.)	250 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	125.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %


Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	2 W
Lamp current (nom.)	20 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	30 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear

# CorePro GLASS LED candles and lustres

Bulb shape	P45 [ P 45mm]
<b>Approval and Application</b>	
Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	2 kWh
	387364
<b>Product Data</b>	
Full product code	871951434776200

Order product name	CorePro LEDLusterND2-25W P45 E27 827 CLG
EAN/UPC – product	8719514347762
Order code	34776200
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929001238792
SAP net weight (piece)	0.012 kg


## Dimensional drawing




CorePro LEDLusterND2-25W P45 E27 827 CLG

Product	D	C
CorePro LEDLusterND2-25W P45 E27 827 CLG	45 mm	78 mm

## Photometric data




LED Lamps, Lightcolour /827 ND CL



Classic LEDCandle ND 2-25W P45 827 CL

# CorePro GLASS LED candles and lustres

## Photometric data




CalcXpert Photometrics 4.5 Philips Lighting B.V. Page 5/7

### Classic LEDCandle ND 2-25W P45 827 CL

## Lifetime



### 15K LED



### 15K LMP

