

RAS-CBNO

Specifications and dimensions



- Contact block for 22mm devices
- Normally open configuration

Features	
Length	30mm
Width	13mm
Depth	24mm
Weight	0.014Kg
Rated thermal current I _{th}	10A
Rated insulation voltage U _i	500V
Operating force	10N
Operating force additional contacts	5N
Cable capacity	2 x 1.5mm ²
Contact operation	Slow action, positive opening
Related products	
Normally closed contact	RAS-CBNC
NO contact for plastic boxes	RAS-BCBNO
NC contact for plastic boxes	RAS-BCBNC

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>