




The Belkin OmniView USB CAT5 Extender allows you to control your computer or KVM switch from up to 500 feet (150m) away. It is perfect for isolated server rooms, large server farms, secure systems, or test benches where the computer or KVM switch may be inaccessible to the user.

The CAT5 Extender significantly reduces cable bulk and simplifies cable management with CAT5 technology. The Extender also features both local and remote console accessibility with an optional 2-port KVM function at the remote terminal (additional cables required).



## Benefits

### CAT5 Technology

- Integrated CAT5 technology enables you to connect your KVM switch to your servers up to 500 feet (150m) away using standard CAT5 cabling. CAT5 cabling reduces cable bulk and simplifies cable management.

### Video Resolution

- The CAT5 Extender supports video resolutions of up to 1920x1440@75Hz on local computers and up to 1280x1024@75Hz on remote.

### Local and Remote Ports

- The CAT5 Extender features local and remote console ports, enabling you to control your computers from near or far.

### Built-In Cabling

- A built-in, 3-foot, all-in-one KVM cable provides an easy connection between the CAT5 Extender and your computer or KVM switch.

### LED Display

- An LED display on the transmitter and receiver units provides quick status monitoring. A power LED indicates power is being supplied to the unit. A flashing LED indicates whether the data is being transmitted.

### Recommended Cables:



### KVM Universal Cable Kit: VGA & USB

Allows you to connect an optional computer to the receiver unit at the remote terminal.

- F1D9006-06 Universal KVM Cable Kit, USB 6 ft.
- F1D9006-10 Universal KVM Cable Kit, USB 10 ft.
- F1D9006-15 Universal KVM Cable Kit, USB 15 ft.

### Receiver Unit



- Local CPU Console Connectors
- Local Computer (Requires additional cable to connect)
- RJ45 CAT5 Port for Remote Computer Connection
- Power Jack

### Transmitter Unit



- Local Console Connectors
- RJ45 CAT5 Port for Remote Computer Connection

### Package Contents

- USB CAT5 Extender Transmitter
- USB CAT5 Extender Receiver
- 5V AC, 2.5A Power Supply
- User Manual

### Product Specifications

Part No.	F1D086Uea
Enclosure	Metal enclosure
Receiver Power	5V, 220mA (from attached computer or KVM switch via keyboard port)
Max. Video Remote Resolution	Up to 1280x1024 @ 75Hz (depends on cable length)
Max. Video Local Resolution	Up to 1920x1440 @ 75Hz
Keyboard Emulation	USB
Mouse Emulation	USB
Console Keyboard Input	USB Type A
Console Mouse Input	USB Type A
Console Monitor Port	HDDB15 female (VGA)
CPU Keyboard/Mouse Port	USB Type B
CPU Monitor Port	HDDB15 female (VGA)
CAT5 Extension Ports	RJ45
Operating Temp	32° to 104° F (0° to 40° C)
Storage Temp	-4° to 140° F (-20° to 60° C)
Humidity	0-80% RH, non-condensing
Warranty	2 years
Dimensions	Transmitter: 5.2 x 2.2 x 1.2 in. (132 x 55 x 30mm) Receiver: 7.8 x 2.8 x 1.2 in. (198 x 70 x 30mm)
Weight	Transmitter: 8.0 oz. (0.23kg.) Receiver: 12.3 oz. (0.35kg.)

### Part Number

F1D086Uea

### Description

OmniView USB CAT5 Extender

### UPC

7-22868-65183-4