



40" Full HD LED Digital TV with Built-in DVD Player and Freeview T2 HD

- 40" Full HD widescreen LED TV
- Built-in Freeview T2 HD and Digital Freeview Channels
- Built-in DVD Player
- 3 x HDMI inputs for your external devices and consoles
- Can be wall mounted (200mm x 200mm)

	EAN	5060062269505
Specifications	Model No.	C4020F
	Chipset	MSD3663LSA
	Sales Market	England
	VESA Size	200 x 200
	Wall Mount Screws	M5 x 8
	Speaker Output	2 x 8w
	Actual Size of Display (Diagonal)	40"

Display	Display Type	LED
	Resolution	1920 x 1080 (16:9)
	Brightness (nit)	200
	Contrast	3500:1
	Display Colours	16.7M
	Refresh Rate	60Hz
	Viewing Angle H/V	178/178
	Response Time	8ms

Terminals	RF Antenna	1
	HDMI	x3
	CVBS	YES x 1(3.5 φ Mini Jack)
	PC In	x1
	Audio In	PC audio x 1(3.5 φ Mini Jack), CVBS Audio x1(Mini Jack, Shared with Ypbpr)
	Scart	x1
	YPbPr	YES x 1(3.5 φ Mini Jack)
	Digital Audio out	x1
	Earphone Out	x1
	USB on TV	x1
	CI	x1

Accessories	Remote	1
	Battery	AAA x 2

Other Features	DVB-S	Without
	DVB-S2	Without
	DVB-T	With
	DVB-T2	With
	CI	With
	DVD	With
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
	PVR Function	Recording standby, time-shift EPG recording reservation

Power	Power Supply	AC 100V-240V - 50Hz/60Hz
	Operation Power Consumption	58W
	KWh/annum	85kWh
	Max Power Consumption	70W
	Energy Efficiency Class	F

Dimension	Unit Dimension With Stand	907.99 x 571.26 x 257.38
	Unit Dimension Without Stand	907.99 x 528.23 x 81.41
	Carton Box Dimension	1015 x 650 x 160
	Weight of Unit (kg)	7.2