



50" 4K Ultra HD LED Digital TV with Built-in Freeview T2 HD

- 50" 4K UHD widescreen LED TV
- Built-in Freeview T2 HD and Digital Freeview Channels
- 3 x HDMI inputs for your external devices and consoles
- Can be wall mounted (400mm x 400mm)

	EAN	5060062269871
Specifications	Model No.	C5020DVB4K
	Chipset	3683
	Sales Market	England
	VESA Size	400 x 400
	Wall Mount Screws	M6 x 10
	Speaker Output	2 x 8w
	Actual Size of Display (Diagonal)	50"

Display	Display Type	LED
	Resolution	3840 x 2160
	Brightness (nit)	220
	Contrast	5000:1
	Display Colours	1.07G colour
	Refresh Rate	60Hz
	Viewing Angle H/V	178/178
	Response Time	9.5ms

Terminals	HDMI Input	3
		480i, 480p, 586i, 576p, 720p, 1080i, 1080p, 4k
		(CEC, ARC)
	SCART	1
	EARPHONE	1
	RCA Component + AUDIO Input	1
	RCA Composite + AUDIO Input	1
	Optical Digital AUDIO Output	1
	RF Input	1

Accessories	Remote	1
	Battery	AAA x 2
	User Manual	English

Other Features	DVD Player	No
	DVB-S	Without
	DVB-S2	Without
	DVB-T	With
	DVB-T2	With
	CI	With
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/ Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
	PVR Function	Recording standby, time-shift
EPG recording reservation		

Power	Power Supply	AC 120V-230V, 50Hz/60Hz
	Power Consumption	130W
	Standby Power Consumption	<0.5W
	Energy class	G

Dimensions	Unit Dimension With Stand	1128.2 x 286.2 x 706.9
	Unit Dimension Without Stand	1128.2 x 89.5 x 653.9
	Carton Box Dimension	1230 x 790 x 170