



19" HD LED Digital TV with Built-in DVD Player and Satellite Tuner

- 19" HD Ready widescreen LED TV
- Built-in Freeview HD and Digital Freeview Channels
- Built-in Satellite Tuner
- Built-in DVD Player
- HDMI input for your external devices and consoles
- Can be wall mounted (100mm x 100mm)

	EAN	5060750400876
Specifications	Model No.	C1920FS
	Chipset	MSD3663
	Sales Market	UK
	VESA Size	100 x 100
	Wall Mount Screws	M4 x 6
	Speaker Output	2 x 3W
	Actual Size of Display (Diagonal)	18.5"
	Display	Display Type
Resolution		1366 x 768 (16:9)
Brightness (nit)		200
Contrast		1000:1
Display Colours		16.7M
Refresh Rate		60Hz
Viewing Angle H/V		89/89/89/89
Reponse Time		14ms
Accessories	Remote	1
	Battery	AAA x 2
	User manual	N/A

Terminals		
	HDMI Input	1
	RCA Component + AUDIO Input	1
	RCA Composite + AUDIO Input	1
	15-PIN VGA + AUDIO Input	1
	RF Input	2
	Optical Digital AUDIO output	1
	Coaxial Digital AUDIO output	0
	AV Out	1
	3.5mm Headphone Output	1
	USB on TV	1

Features		
	DVD	Yes
	DVB-S	Yes
	DVB-S2	Yes
	DVB-T	Yes
	DVB-T2	Yes
	CI	Yes
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	No Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
	PVR Function	Recording standby, time-shift EPG recording reservation

Power		
	Power Supply	AC 100V-240V ~ 50Hz/60Hz
	Operation power consumption	17W
	KWh/annum	25kWh
	Max Power Consumption	36W
	Standby Consumption	<0.5W
	Energy class	F

Dimensions		
	Unit Dimensions w Stand	446 x 160 x 322
	Unit Dimensions w/o Stand	446 x 68 x 266
	Carton Box Dimensions	2.9