

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

High-pressure Washer

GHP 5-65 X



Powerful and versatile: A compact, mobile and powerful high-pressure washer with practical hose reel

The most important data

Operating pressure	130 bar
Max. pressure	160 bar
Rated input power	2,400 W

Part Number 0 600 910 670[> More product information](#)

Technical data

Technical data

Max. pressure	160 bar
Rated input power	2,400 W
Operating pressure	130 bar
Max. inlet temperature	50 °C
Cable length	5 m
Hose length	10 m
Material (hose)	Steel reinforced
Weight (without accessories)	23.6 kg
Rated flow rate	485 l/h
Max. flow rate	520 l/h
Pump system	Wobble plate
Pistons	Triple stainless steel
Motor type	Induction
Packaging dimensions (width x length x height)	440 x 785 x 398 mm
Voltage, electrical	240 V

Noise/vibration information

Total vibration values

Vibration emission value ah	1.8 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High cleaning power: Aluminium anodised pump with stainless steel pistons producing a combination of high flow and pressure resulting in high cleaning power
 - Convenient: Metal telescopic handle for ease of use.
Mobile and space-saving due to hose reel
 - Versatile: Used both in horizontal and vertical positions
-