

Plateswitches

DP FLUSH
20 AMP



K4867WHI



K4868WHI

Lockable Fire Alarm Isolator Switch

DP FLUSH
20 AMP



K4780WHI

Architrave Switches

FLUSH
10 AMP



K4841WHI



K4842WHI



K4848BWHI



K4848PWHI

Wide Rocker Switches

FLUSH
10 AMP



K4781GRA



K4782GRA



K4783WHI



K4785WHI

K4867WHI 10
1 GANG DP
K4868WHI 10
2 GANG DP

MOUNTING BOXES
866ZIC
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS EN 60669-1:1999

K4780WHI 1
20A DP LOCKABLE FIRE
ALARM ISOLATOR SWITCH

MOUNTING BOXES
866ZIC
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS 60669-2-4:2005

K4841WHI 5
1 GANG SP
TWO-WAY
K4842WHI 5
2 GANG SP
TWO-WAY
K4848BWHI 5
1 GANG SP PUSH SWITCH
WITH BELL SYMBOL
PUSH TO MAKE OR BREAK
K4848PWHI 5
1 GANG SP PUSH SWITCH
MARKED 'PRESS'
PUSH TO MAKE OR BREAK

MOUNTING BOXES
FLUSH
1 GANG: 3921ZIC
2 GANG: 3922ZIC
SURFACE
1 GANG: k2151WHI
2 GANG: k2152WHI
These switches do not have to be derated
when used with fluorescent or inductive loads.
K4841, K4842 These switches can be wired
as either one-way or two-way.
DIMENSIONS
1 GANG: 86 x 32mm;
2 GANG: 146 x 32mm
FIXING CENTRES
1 GANG: 60.3mm;
2 GANG: 120.6mm
BS EN 60669-1:1999

K4781WHI 10
K4781GRA 10
1 GANG SP TWO-WAY
WITH WIDE ROCKER
K4782WHI 10
K4782GRA 10
2 GANG SP TWO-WAY
WITH WIDE ROCKERS
K4783WHI 10
3 GANG SP TWO-WAY
WITH WIDE ROCKERS
K4785WHI 10
K4785GRA 10
1 GANG SP INTERMEDIATE
WITH WIDE ROCKER
K4787WHI 10
1G 20A DP ONE-WAY
WITH WIDE ROCKER
K4788WHI 10
2 GANG DP WITH
WIDE ROCKER

MOUNTING BOXES
FLUSH
861ZIC
SURFACE
K2160WHI
K2140WHI (for extra
wiring space)
These switches do not
have to be derated when
used with fluorescent
or inductive loads.
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS EN 60669-1:1999
20A DP VERSIONS
K4787WHI is 20A DP
1 way version of K4781.
BS EN 60669-1: 1999
K4788WHI is 20A DP
1 way version of K4782.
BS EN 60669-1:1999