

Blank Plates

Flex Outlet
FrontplateEuro Modular
FrontplatesEuro Power
Modules

20 AMP



K3825WHI

K3827WHI



K3828WHI



K5033WHI




K1090WHI



K181WHI




K182WHI



K184WHI



K5830WHI



K5831WHI



K5832WHI



K5833WHI



K5834WHI



K5837WHI

- K3825WHI** 10
1 GANG MOULDED
ARCHITRAVE
- K3827WHI** 10
1 GANG MOULDED
- K3828WHI** 10
2 GANG MOULDED
- K5033WHI** 1
METAL

K3825WHI
For use with 3921ZIC and K2151WHI
MOUNTING BOXES.

K5033WHI
For use with 5120ALM deep metal box.

DIMENSIONS
K3825WHI: 86 x 31mm
K3827WHI: 86 x 86mm
K3828WHI: 86 x 146mm
K5033WHI: 178 x 165mm

FIXING CENTRES
K3825WHI: 60.3mm
K3827WHI: 60.3mm
K3828WHI: 120.6mm
K5033WHI: 133mm
BS 5733:2010

- K1090WHI** 10
FLEX OUTLET FRONTPLATE
UNFUSED

Complete with three pairs of terminals, each suitable for 2 x 2.5mm² conductors and a 1.5mm² flexible cord. A cord-grip is also fitted.

Frontplate thickness is 12.5mm.
Cable entry diameter is 11mm.

DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS EN 60670-22:2006

- K181WHI** 10
1 GANG EURO FRONTPLATE
ONE MODULE

APERTURE SIZE 25 X 50MM

- K182WHI** 10
K182GRA 10

1 GANG EURO FRONTPLATE
TWO MODULE

APERTURE SIZE 50 X 50MM

- K184WHI** 10
K184GRA 10

2 GANG EURO FRONTPLATE
FOUR MODULE

APERTURE SIZE 100 X 50MM

- K185WHI** 10

3 GANG EURO FRONTPLATE
SIX MODULE

APERTURE SIZE 150 X 50MM

MOUNTING BOXES
Suitable for flush boxes to BS 4662:2006 and surface boxes to BS 5733:2010 Refer to appropriate module for minimum box depth.

K185WHI MOUNTING BOX
35mm VTS8035 (For use with Pinnacle and Premier cable management systems) K2153WHI 30mm

FIXING CENTRES
1 GANG: 60.3mm 2 GANG: 120.6mm
BS 5733:2010 where applicable
Note: No grid required, modules just clip into place

- K5830WHI** 1
K5830BLK 1

UK 1 GANG EURO 2 MODULE

13A 250V SHUTTERED

- K5831WHI** 10
K5831BLK 10

GERMAN 2P+E

16A 250V SHUTTERED

EURO 2 MODULE (NON UK)

- K5832WHI** 10
K5832BLK 10

AMERICAN 2P+E

15A 127V SHUTTERED

EURO 2 MODULE (NON UK)

K5830 MOUNTING BOX
35mm minimum
46mm (for extra wiring space)

DIMENSIONS
50 x 50mm
BS 1363 Pt2:1995

K5831 MOUNTING BOX
46mm

DIMENSIONS
50 x 50mm
IEC 60884-1:2006

K5832 MOUNTING BOX
35mm
46mm (for extra wiring space)

DIMENSIONS
50 x 50mm
SASO 2204:2003

- K5833WHI** 10
K5833BLK 10

UK 1 GANG EURO 2 MODULE

5A 250V SHUTTERED

- K5834WHI** 10
K5834BLK 10

FRENCH/BELGIAN 2P+E

16A 250V SHUTTERED

EURO 2 MODULE (NON UK)

- K5837WHI** 1
K5837BLK 1

USB CHARGING MODULE

EURO 2 MODULE

K5833 MOUNTING BOX
35mm minimum
46mm (for extra wiring space)

DIMENSIONS
50 x 50mm
BS 546:1950

K5834 MOUNTING BOX
46mm

DIMENSIONS
50 x 50mm
NF C61-314

K5837 MOUNTING BOX
35mm, 46mm (for extra wiring space)

DIMENSIONS
50 x 50mm
USB charging sockets, each capable of supporting 2A charge (total of 2A).
IEC 60950-1
IEC 61000-6-1/3