

Description:

16A Double Pole Neon Half Euro Module Switch

Features:

PE507

- For use with Easy Clip face plates
- Durable polycarbonate construction

**Technical:**

Neon	Yes
Intermediate switch	No
Retractive switch	No
Colour	White
Compliance	CE Compliant 93/68/EEC
Current rating	16A
Material	Polycarbonate
Frequency	50/60 Hz
Guarantee	2 Years
Manufacturer	RPP
Number of ways	1 Way
Packaging	Each
Standards	BS EN 60669
Terminal capacity live/neutral	3 x 2.5mm ²
Voltage rating	230V
Product type	ROHS 2011/65/EU