



TV/Radio/Sat

Art. Number 304102



- Triplexed (TV/Radio/Sat)
- Fully screened
- UK style front plate
- Die-cast housing
- DAB compatible

## Technical Specifications

### ORDER INFORMATION

EAN Number 5702663041028

### FREQUENCY RANGE

Frequency Range FM | MHz 87.5...230 MHz  
Frequency Range TV | MHz 47...68/254...862 MHz  
Frequency Range SAT | MHz 950...2400 MHz

### LOSS

Through Loss IN-FM | dB <3.0 dB  
Through Loss IN-TV | dB <2.5 dB  
Through Loss IN-SAT | dB <3.0 dB

### OPERATIONAL

DC Passthrough SAT Yes

### CONNECTORS

Connector IN-OUT Spring Clamp Termination  
Connector FM IEC-female  
Connector TV IEC-male

### MECHANICAL

Product Height | mm 86 mm  
Product Width | mm 86 mm  
Product Depth | mm 35 mm



## Technical Specifications

|                                   |                           |
|-----------------------------------|---------------------------|
| Packaging Height   m              | 0.455 m                   |
| Packaging Width   m               | 0.260 m                   |
| Packaging Depth   m               | 0.505 m                   |
| Packaging Volume   m <sup>3</sup> | 0.060 m <sup>3</sup>      |
| Net Weight   kg                   | 0.138 kg                  |
| Tara Weight   kg                  | 0.035 kg                  |
| Total Weight   kg                 | 0.173 kg                  |
| Remarks                           | Screened Die-Cast housing |