

List No. VX3800SS

FLAT PLATE DECORATIVE

20VA Dual Voltage Shaver Supply Unit White Interior
Stainless Steel Finish



- Dual Voltage
- Stainless Steel Finish
- White Interior
- Interior for Plate or Panel Mounting

Product Specification Data		Revision Date: 15/10/2021
Product Standard/s	BS EN 61558-2-5	
Terminal Capacity L&N	4 x 1.0, 3 x 1.5 mm ²	
Terminal Capacity E	4 x 1.0, 3 x 1.5 mm ²	
Frequency	50 Hz	
Printing	Shavers Only, Shaver Symbol, 115V, 20VA, 230V	
CE Conformity	Yes	
WEEE Symbol	Yes	
UKCA Conformity	Yes	
Assembly arrangement	Basic element	
Mounting method	Surface mounted (plaster)	
Nominal voltage low value	115 V	
Nominal voltage high value	230 V	
Material	Metal	
Material quality	Stainless steel	
Halogen free	Yes	
Surface protection	Other	
Surface finishing	Matt	
Colour	Stainless Steel	
Width of device	84.4 mm	
Height of device	145.6 mm	
With built-in installation box	No	
Min. depth of built-in installation box	47 mm	

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.