



- Dual Voltage
- 1 x American Shaver Plug
- 1 x British Shaver Plug

Product Specification Data

Revision Date: 15/10/2021

Product Standard/s	BS EN 61558-2-5
Terminal Capacity L&N	4 x 1.0, 3 x 1.5 mm ²
Terminal Capacity E	4 x 1.0, 3 x 1.5 mm ²
Frequency	50 Hz
LRV Value	74
Printing	Shaver Symbol, Vorex, 'shavers only', 115V, 230V, 20VA
CE Conformity	Yes
WEEE Symbol	Yes
UKCA Conformity	Yes
Assembly arrangement	Basic element
Mounting method	Surface mounted (plaster)
Nominal voltage low value	115 V
Nominal voltage high value	230 V
Material	Plastic
Material quality	Other
Halogen free	Yes
Surface protection	Other
Surface finishing	Glossy
Colour	White
Width of device	91 mm
Height of device	151 mm
With built-in installation box	No
Min. depth of built-in installation box	47 mm

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.