

SPECIFICATION SHEET



LED CIRCULAR WALLWASHER SHOPLIGHT

The recessed LED Circular Wallwasher Shoplight is ideal for applications such as shopping centres and reception areas. The 40° tilt angle and 45° beam angle make it perfect for feature lighting.

Applications:

• Leisure Centres • Hospitality • Retail




Specification

LED:	Citizen COB
Material:	Aluminium
Lumen Output:	2900lm
Colour Temperature:	4000K
Guarantee:	3 Years
Life Expectancy:	50,000 Hours
Working Temperature:	-20°C - 65°C
Beam Angle:	45°
CRI:	>80 Ra

Additional Information

- 40° Tilt angle.
- 90% Energy saving compared to incandescent lamp.
- 350° Rotation.
- Dimmable driver (LEDDRIVER36D) available.
- Emergency conversion (EMLEDKIT2) available.
- EMLEDKIT2 - 193lm in emergency mode.
- Environmentally friendly.
- Good heat dissipation.
- White finish.

Dimensions



Code	Wattage	Lumen Output	Dimensions (Ø x D mm)	Cut out (Ø mm)
SLCT30W-40	30W	2900lm	190 x 130	170