



List No. B20 STANDARD RANGE

20A SP Type B 6kA MCB, Standard



- Spare plug in MCB, 20A
- Wylex Standard range
- Colour coded yellow

Product Specification Data

Revision Date: 15/10/2021

Release characteristic	B
Number of poles (total)	1
Number of protected poles	1
Rated current	20 A
Rated voltage	230 V
Rated insulation voltage U_i	400 V
Rated impulse withstand voltage U_{imp}	4 kV
Rated short-circuit breaking capacity I_{cn} EN 60898 at 230 V	6 kA
Rated short-circuit breaking capacity I_{cn} EN 60898 at 400 V	3 kA
Voltage type	AC
Frequency	50 Hz
Current limiting class	1
Suitable for flush-mounted installation	No
Concurrently switching N-neutral	No
Over voltage category	3
Additional equipment possible	No
Width in number of modular spacings	1
Product Standard/s	BS EN 60898-1
CE Conformity	Yes
WEEE Symbol	Yes
UKCA Conformity	Yes

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.