



## List No. NMRS6606LA

NH / NM / NMX

12 Way Split Load Consumer Unit 100A Main Switch +6, 80A  
30mA RCD +6



- Full metal enclosure
- Fixed busbar assembly
- 6+6W Split load
- 1x 80A 30mA type A RCCB

Product Specification Data		Revision Date: 15/10/2021
Mounting method	Surface mounted (plaster)	
Number of phases	1	
Protection	Miniature- / earth leakage circuit breaker	
Total number of groups	2	
Number of poles main switch	2	
Main switch rated current	100 A	
Over voltage protection	No	
Material housing	Steel	
Degree of protection (IP)	IP2XC	
Height	261 mm	
Width	343 mm	
Width in number of modular spacings	16	
Depth	121 mm	
Extension possible	No	
With transparent cover	No	
Lockable	Yes	
Product Standard/s	BS EN 61439-3	
Frequency	50 Hz	
CE Conformity	Yes	
WEEE Symbol	Yes	
UKCA Conformity	Yes	
Amperage	100 A	
Operating Voltage	230 V	
Type of Current	AC	
Consumer Unit Type	Split load	
Total final circuit modular ways	12	
Busbar type	Fixed	
Main switch rating	100 A	
Main switch final circuit modular ways	6	

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.

RCD 1	80A 30mA type A
RCD 1 final circuit modular ways	6
Colour RAL	9010

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.



**Electrium Sales Limited**, Walkmill Lane, Cannock WS11 0XE  
01543 455000 [www.electrium.co.uk](http://www.electrium.co.uk) [info@electrium.co.uk](mailto:info@electrium.co.uk)