

Wireless Keyboard 850 with AES



Name Information	
Product Name	Microsoft® Wireless Keyboard 850 with AES
Keyboard Name	Microsoft Wireless Keyboard 850 with AES
Transceiver Version	Microsoft 2.4 GHz Transceiver v8.0
Product Dimensions	
Keyboard Length	19.1 inches (486 millimeters)
Keyboard Width	8.93 inches (227 millimeters)
Keyboard Depth/Height	1.79 inches (45.7 millimeters)
Keyboard Weight	21.2 ounces (601 grams) includes 2 AA alkaline batteries; typical battery weight may vary
Transceiver Length	1.09 inches (27.6 millimeters)
Transceiver Width	0.59 inches (15.0 millimeters)
Transceiver Depth/Height	0.27 inches (6.89 millimeters)
Transceiver Weight	0.09 ounces (2.8 grams)
Compatibility and Localization	
Interface	USB 2.0 Compatible
Operating Systems ¹	<ul style="list-style-type: none"> • Microsoft Windows® 10 / 8.1 / 8 / RT 8.1 / RT 8 / 7 • Microsoft Windows 10 Phone • Mac OS X 10.7 - 10.10 • Android 3.2 - 5.0 <p>¹Advanced functionality not available with all devices. See compatibility information at: microsoft.com/hardware/compatibility</p>
Customizable features available for Windows	<p>Requires Mouse and Keyboard Center software installed on a PC that meets the requirements and has one of these operating systems:</p> <ul style="list-style-type: none"> • Microsoft Windows 10 / 8.1 / 8 / RT 8.1 / RT 8 / 7 • 150 MB of available hard disk space <p>You must accept License Terms for software download at microsoft.com/hardware/downloads. Broadband required. Added charges may apply.</p>
Compatibility Logos	<ul style="list-style-type: none"> • Compatible with Microsoft Windows 10 / 8 / 7 • Mac logo
Software Localization	<p>For a Microsoft Windows-based PC: Microsoft Mouse and Keyboard Center software may be installed in Simplified Chinese, Traditional Chinese, English, French, German, Italian, Japanese, Korean, Brazilian Portuguese, Iberian Portuguese, or Spanish. If available, standard setup will install the software in the default OS language. Otherwise, the English language version will be installed.</p> <p>For a Macintosh PC: Microsoft IntelliType Pro for Mac and Microsoft IntelliPoint for Mac will install in English, French, German, Italian, Japanese, Brazilian Portuguese, and Spanish. User settings for OS language preference determine which localized version of the software is displayed. In the event that OS language preferences are not supported, the English language version will be displayed.</p>
Keyboard Localization	<p>Available language sets will vary by product and sales channel.</p> <p>104 key configuration: Arabic, Chinese (Simplified), Chinese (Traditional), Czech, English (Canada), English (North America), Greek, Hebrew, International English (Euro), International English (ROW), Russian, and Thai</p> <p>105 key configuration: All Nordic, English (UK), French (Belgium/Azerty), French (Canada), French (France), German (Germany), German (Switzerland/Luxemburg), Hungarian, Iberian (Portuguese), Italian, Spanish (Euro), Spanish (Latin America), and Turkish</p> <p>106 key configuration: Korean</p> <p>107 key configuration: Brazilian</p> <p>109 key configuration: Japanese</p>
Wireless Technology	
Wireless Frequency	2.4 GHz frequency range
Wireless Range	15 feet (5 meters) typical. Note: RF range is affected by many factors, such as nearby metallic objects and relative positioning of the mouse and receiver.
Product Feature Performance	
QWERTY Key Life	5,000,000 actuations per key
Encryption Features ²	128-bit AES encryption
Hot Key Features	Windows 8 Charms keys, Windows Start key, and Calculator
Hot Key Life	500,000 actuations per key
Media Key Features	Mute, Volume -, Volume +, and Play/Pause
Media Key Life	500,000 actuations per key
Typing Speed	1000 characters per minute
Storage Temperature & Humidity	-40 °F (-40 °C) to 140 °F (60 °C) at < 5% to 65% relative humidity (non-condensing)
Operating Temperature & Humidity	32 °F (0 °C) to 104 °F (40 °C) at < 5% to 80% relative humidity (non-condensing)
Power Requirements	
Battery Type and Quantity	• 2 AAA alkaline batteries (included)
Battery Life	• 15 months typical
Certification Information	
Country of Manufacture	People's Republic of China (PRC)
ISO 9001 Qualified Manufacturer	Yes
ISO 14001 Qualified Manufacturer	Yes
Restriction on Hazardous Substances	This device complies with all applicable worldwide regulations and restrictions including, but not limited to: EU directive 2002/95/EC on the Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment and EU Registration Evaluation and Authorization of Chemicals (REACH) regulation regarding Substances of Very High Concern.
FCC/IC ID	This Class B digital apparatus complies with Part 15 of the U.S. Federal Communications Commission (FCC) rules, Canadian ICES-003, and RSS-210. Operation is subject to the following two conditions: (1) this device may not cause interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Tested to comply with FCC (U.S. Federal Communications Commission) Standards. For home or office use. The term "IC:" before the certification/registration number only signifies that the Industry Canada technical specifications were met. Model numbers: 1455, Wireless Keyboard 850; 1454, Wireless Mobile Mouse 1000 and 1461, Microsoft 2.4GHz Transceiver v8.0, FCC IDs: C3K1455, C3K1454, and C3K1461. IC IDs: 3048A-1455, 3048A-1454, and 3048A-1461.
Regulacion para México	La operación de este equipo está sujeta a las siguientes dos condiciones: (1) es posible que este equipo o dispositivo no cause interferencia perjudicial y (2) este equipo o dispositivo debe aceptar cualquier interferencia, incluyendo la que pueda causar su operación no deseada.

Certification Information		
Agency and Regulatory Marks	<ul style="list-style-type: none"> • CNC Certificate (Argentina) • ACA/MED Declaration of Conformity (Australia and New Zealand) • DWLFM Certificate (Bahrain) • ANATEL Certificate (Brazil) • IC ID, Certificate of Acceptance (Canada) • SUBTEL Certificate (Chile) • CMIIT Certificate (China) • EIP Pollution Control Mark, EPUP (China) • Indotel Certificate (Dominican Republic) • R&TTE Declaration of Conformity, Safety and EMC (European Union) • WEEE (European Union) • NTRA Certificate (Egypt) • Conatel Certificate (Honduras) • ETA Certificate (India) • POSTEL Certificate (Indonesia) • MOC Certificate (Israel) • VCCI and Telec Certificates (Japan) • TRC Certificate (Jordan) • CCK Certificate (Kenya) • KCC Certificate (Korea) • MPT Certificate (Kuwait) • MOT Certificate (Lebanon) • SIRIM Certificate (Malaysia) 	<ul style="list-style-type: none"> • ICTA Certificate (Mauritius) • COFETEL Certificate (Mexico) • ANRT Certificate (Morocco) • NCC Certificate (Nigeria) • TRA Certificate (Oman) • PTA Certificate (Pakistan) • MTC Certificate (Peru) • ICT Certificate (Qatar) • FAC and EAC Certificates (Russia) • CIRC Letter (Kingdom of Saudi Arabia) • RATEL Certificate (Serbia) • IDA Registration (Singapore) • ICASA Certificate (South Africa) • BSMI and NCC Certificates (Taiwan) • SDoC Certificate (Thailand) • CERT Certificate (Tunisia) • TRA Certificate (United Arab Emirates) • UkrSEPRO Certificate (Ukraine) • URSEC Certificate (Uruguay) • FCC ID, Grant of Equipment Authorization (USA) • CONATEL Certificate (Venezuela) • CB Scheme Certificate (International)
Warranty	3 years	
Windows Certification Kit (WCK)	Desktop ID: 1731369 (32-bit) and (64-bit) Microsoft Windows 10	