

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0008500113**  
**Status:** **Active**  
**Overview:** KK Interconnect Solutions  
**Description:** KK 254 Crimp Terminal, 22-30 AWG, Hot Tin (Sn) Dip Plating

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-2759-002-001 (PDF)</a>
<a href="#">Product Specification 50510002-PS-000 (PDF)</a>	<a href="#">Test Summary TS-10-07-001 (PDF)</a>
<a href="#">Product Specification PS-10-07-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<u>2759</u>
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	<u>KK Interconnect Solutions</u>
Packaging Alternative	<u>08500114 (Loose)</u>
Product Name	KK 254
UPC	800753614444

**Physical**

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.065/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm <sup>2</sup>	N/A

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

Engineering Number	2759-(P909)B
--------------------	--------------

**Reference - Drawing Numbers**

Packaging Specification	PK-2759-002-001
Product Specification	50510002-PS-000, PS-10-07-001
Sales Drawing	SD-2759-001
Test Summary	TS-10-07-001



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)10043-DC (17  
Jan 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

2759 Series

**Use With**

2695 , 5051

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Extraction Tool for KK 2.54mm Terminals, 22-30 AWG	<u>11030022</u>
Terminator Die	<u>11402265</u>
Insertion Tool for KK 2.54mm Terminals, 22-30 AWG	<u>638120000</u>
Mini-Mac Applicator for KK and Cat Ear Terminals for 22-30	<u>638882000</u>

AWG Wire with  
Insulation Diameter  
1.09-1.57mm  
and 22-28  
AWG Wire with  
Insulation Diameter  
1.20-1.70mm  
Mini-Mac Applicator [638882100](#)  
for KK and Cat Ear  
Terminals for 22-30  
AWG Wire with  
Insulation Diameter  
0.96-1.20mm

This document was generated on 03/14/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**