


TURFAL-6-FW


6MP IP NETWORK IR TURRET CAMERA



- 6MP [3072 × 2048] H.265 coding
- Max.resolution: 3072 × 2048
- ICR auto switch, true day / night, ROI coding 3D DNR, digital WDR, HLC, BLC, defog
- 20~30m IR night view distance
- 1CH built-in MIC
- Support smart phone, iPad, remote monitoring
- DC12V/PoE power supply
- IP 67 ingress protection
- Support three streams



Optional Accessories



CODE: FAL-RING-03-WH



Lens
2.8mm



Digital
WDR



20-30m IR
Distance



IP67
Weatherproof



H.265
Video
Compression

6MP

6MP
Resolution



Audio



Built-in Mic

TURFAL-6-FW

6MP IP NETWORK IR TURRET CAMERA



SPECIFICATIONS

Camera	
Image Sensor	1 / 2.7 "CMOS
Image Size	3072×2048
Electronic Shutter	1 / 25 s ~ 1 / 100000 s
Iris Type	Fixed Iris
Min. Illumination	0.0236 lux @F2.0, AGC ON; 0 lux with IR 0.0085 lux @ F1.2, AGC ON; 0 lux with IR
Lens	2.8 mm @F2.0, horizontal field of view: 93.4°
Lens Mount	M12
Wide Dynamic Range	Digital WDR
BLC	Yes
HLC	Yes
Defog	Yes
Digital NR	3D DNR
Angle Adjustment	Pan: 0°~360°; Tilt:0°~75°; Rotation: 0°~360°
Image	
Video Compression	H.265 / H.264
H.265 Compression Standard	Main Profile@Level4.1 High Tier
Resolution	6MP (3072×2048), 4MP (2560 × 1440),1080P (1920 × 1080), 720P (1280 × 720), D1, CIF, 480 × 240
Main Stream	60Hz : 6MP(1~20fps)/4MP(1~30fps)/1080P(1~30fps)/ 720P(1~30fps) 50Hz : 6MP(1~20fps)/ 4MP(1~25fps)/1080P(1~25fps)/ 720P(1~25fps)
Sub Stream	60Hz : 720P(1~15fps)/D1(1~30fps)/CIF (1~30fps); 50HZ:720P(1~12fps)/D1(1~25fps)/CIF (1~25fps)
Third Stream	60Hz : D1/CIF/480x240 (1~30fps); 50HZ: D1/CIF/480x240 (1~25fps)
Bit Rate	128 Kbps ~ 5 Mbps
Bit Rate Type	VBR / CBR
Audio Compression	G711A / U
Image Settings	ROI, Saturation, Brightness, Chroma, Contrast,Wide Dynamic, Sharpen, NR,etc. adjustable through client software or web browser
ROI	Each ROI to be configured separately
Interfaces	
Network	RJ45
Video Output	No
Audio	1CH built-in MIC
Storage	No
Hardware Reset	No
Functions	
Remote Monitoring	Web browsing,CMS remote control
Online Connection	Support simultaneous monitoring for up to 4 users; Support multi-stream real time transmission
Network Protocol	UDP, IPv4, IPv6, DHCP, NTP, RTSP, PPPoE, DDNS, SMTP, FTP, 802.1x, UPnP, QoS
Interface Protocol	ONVIF, GB-T/28181-2011
Storage	Network remote storage
Smart Alarm	Motion detection
General function	Watermark, IP address filtering, video mask, heartbeat, password protection
PoE	Yes
IR Distance	20 ~ 30 m
Ingress Protection	IP67

Others

Power Supply	DC12V/PoE
Power Consumption	< 5W
Operating Environment	- 30 °C ~ 60 °C (-22°F~140°F) Humidity: less than 95 % (non-condensing)
Dimensions (mm)	Φ 94.6 × 82.8
Weight (net)	Approx. 0.45KG
Installation	Ceiling mounting; Wall mounting

DIMENSIONS

