

# Mini Sound Level Meter with Bluetooth

**multicomp** PRO

RoHS  
Compliant



Frequency range	31.5HZ~8KHZ
Accuracy	3dB (under reference condition of 94dB, 1KkHz)
Range:	35~130dB
Measuring range:	LO: 35dB~80dB Med: 50dB~100dB Hi: 80dB~130dB Auto: 35dB~130dB
Fequency weighting	A and C
Microphone	1/2" electret condenser microphone
LCD Display	4 digits LCD display with a resolution: 0.1dB
Display update	2 times / sec.
Operating Temperature and Humidity	0°C ~ 40°C, 10%RH~90%RH
Storage Temperature and Humidity	-10°C~+60°C, 10%RH~75%RH
Bluetooth	Yes
Max / Min	Yes
Auto range selection	Yes
Data Hold	Yes
Backlight	Yes
Over range / Low range indicated	Yes
Low battery indicated	Yes
Auto Power Off	Yes
Power supply	One 9V battery

## Part Number Table

Description	Part Number
Mini Sound Level Meter with Bluetooth	MP780859

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.