



- Marker Ties fasten and provide a surface to identify bundles at the same time.
- Can be marked with *PANDUIT* Marker Pens
- Can be custom imprinted with text, symbols or trademarks using *PANDUIT* Custom Hot Stamping Service.
- Can be marked with Computer Printable Labels.

Part Number:	PLF1MA-C4Y
Product Family:	<i>Pan-Ty</i> ® Marker & Flag Ties - Colors
Product Line:	Marker Cable Ties
RoHS Compliancy Status:	Compliant
Note:	PLF1MA-C4Y replaces PLF1MA-C4
Part Description:	Marker Tie, Flag, 5.1", Miniature cross section
Product Type:	Cable Ties
Material:	Nylon 6.6
Color:	Yellow
CSA Certified:	Yes
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	Yes

Length (In.):	5.1
Length (mm):	130
Width (In.):	.098
Width (mm):	2.5
CE Compliant:	Yes
Cross Section:	Miniature
Head Height (In.):	.154
Head Height (mm):	3.9
Head Width (In.):	.180
Head Width (mm):	4.6
Locking Style:	Locking
Marker Type:	Flag
Marker Write-On Area (In.):	.76 x 1.04
Marker Write-On Area (mm):	19.1 x 26.4
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	.87
Max. Bundle Diameter (mm):	22
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	18

Min. Loop Tensile Strength (N):	80
Std. Pkg. UOM:	PK
Thickness (In.):	.045
Thickness (mm):	1.1
Tool:	GTS, GTSL, GS2B, PTS, PPTS, STS2
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100