

Boxes

Steel Boxes

48MM
SURFACE**K5400WHI**

1

2 GANG
4 X 20MM KNOCKOUTS
4X 25MM KNOCKOUTS

DIMENSIONS

86 x 146mm
FIXING CENTRES
120.6mm
BS 5733:201055MM
FLUSH**5120ALM**

1

FOR FLUSH
COOKER CONTROL UNIT
K5011WHI

Fitted with two earth terminals.

DIMENSIONS
152 x 140 x 55mm

KNOCKOUTS

5 x 25mm.
Two in each of the top & bottom,
one in the back.
BS 4177:199265MM
FLUSH**5268ALM**

1

FOR 32 AMP
TP & N SWITCHES 5114WHI

Fitted with 2 earth terminals

DIMENSIONS
178 x 114 x 65mm

KNOCKOUTS

5 x 25mm.
Two in each of the top and bottom,
one in the back.
BS 5733:201040MM
SURFACE**K829ALM**

5

1 GANG
WITHOUT KNOCKOUTS**K830ALM**

5

2 GANG
WITHOUT KNOCKOUTS**K899ALM**

10

1 GANG
5 X 20MM KNOCKOUTS**K897ALM**

5

2 GANG
8 X 20MM KNOCKOUTSSpares or replacements for the
surface Metalclad Plus range.
All boxes are fitted with an earth
terminal.
BS 5733:2010ARCHITRAVE
FLUSH**3921ZIC**

10

1 GANG

DIMENSIONS

1 gang: 75 x 27 x 27mm
FIXING CENTRES
1 gang: 60.3mm
KNOCKOUTS
1 gang: 3 x 16mm
BS 4662:2006Metal Frames
For Panel
MountingDUAL
FLUSH**887ZIC**

5

DUAL BOX

888ZIC

10

DIVIDING SCREEN
FOR DUAL BOXDual box 887ZIC will accept any two flush
accessories with 86mm square plates and
two M3.5 fixing holes on 60.3mm centres.
Fitted with 2 earth terminals.DIMENSIONS
75 x 161 x 35mm

KNOCKOUTS

2 gang: 10 x 20mm, 4 x 25mm
BS 4662:2006**K2200**

10

1 GANG

K2202

5

2 GANG

FIXING CENTRES
1 gang: 60.3mm
2 gang: 120.6mm
BS 5733:2010

Blank Plates

METALCLAD PLUS™

METALCLAD

**K3390ALM**

10

FOR 1 GANG
SURFACE BOXES
K899 & K829**K3369ALM**

5

FOR 2 GANG
SURFACE BOXES
K830 & K897DIMENSIONS
K3390: 86 x 86mm
K3369: 86 x 147mm

FIXING CENTRES

K3390: 60.3mm
K3369: 120.6mm
BS 5733:2010**3390ALM**

5

FOR 1 GANG SURFACE
BOXES 899 & 829**3370ALM**

10

FOR 1 GANG SURFACE
BOXES 891 & 821**3369ALM**

5

FOR 2 GANG SURFACE
BOXES 892 & 822DIMENSIONS
3390: 81 x 81mm
3370: 76 x 76mm
3369: 76 x 136mm

FIXING CENTRES

1 gang: 60.3mm
2 gang: 120.6mm
BS 5733:2010