

Metalclad Plus™

Features and Benefits



When servicing or repairing appliances fuse carriers on connection units can be padlocked for additional safety



A secret key-operated switch helps prevent unauthorised usage



An optional tamperproof screw on the fuse carrier is particularly useful for appliances in public areas



In-line terminals means that cables can be cut to the same length. White printing gives instant terminal identification



A simple but effective cord grip securely holds the cable in connection units



Backboxes come with or without side knockouts. All boxes have a central knockout in the base for added on-site flexibility

Socket Outlets

127V
(NON UK)
15 AMP



Connection Units

SWITCHED
FUSED
13 AMP



K2271ALM
1 GANG
SHUTTERD
(NON UK)

5

K2272ALM
2 GANG
SHUTTERD
(NON UK)

5

Earth terminal fitted in box.

DIMENSIONS

1 gang 86 x 86 x 47mm

2 gang 86 x 146 x 47mm

KNOCKOUTS

1 gang 6 x 20mm.

Two in one side and one in each of other three sides. One in base

2 gang 8 x 20mm.

Three in top, two in bottom sides and one in each end. One in base

Spare Boxes with and without knockouts are available.

All boxes have a base knockout.

SASO 2204:2003

K963KOALM
DP WITH SECRET KEY OPERATED SWITCH, NEON AND TAMPERPROOF FUSE CARRIER SCREW*

1

K942ALM
DP SWITCHED

5

K942D5ALM
DP SWITCHED WITHOUT BOX

1

K962ALM
DP SWITCHED WITH NEON

5

K962D6ALM
DP SWITCHED WITH NEON AND RED ROCKER

1

Earth terminal fitted in base of the box.

DIMENSIONS

86 x 86 x 47mm

KNOCKOUTS

6 x 20mm.

Two in one side and one in each of other three sides, one in base.

Spare Boxes with and without knockouts are available.

All boxes have a base knockout.

BS 1363-4:1995

* Secret Key - 3405ZIC found on page 223.

K3042WHI
DP SWITCHED WITHOUT BOX

10

K3062WHI
DP SWITCHED WITH NEON WITHOUT BOX

10

All units are supplied with backboxes (except WHI, D5 products and Blankplates)