

# Albany Plus™

mkelectric.co.uk



## Cooker Control Unit

DP MAIN SWITCH  
AND 13 AMP  
SWITCHSOCKET  
OUTLET WITH NEONS  
45 AMP

## Triple Pole & Neutral Switch

32 AMP

## Shaver/Toothbrush Supply Units

DUAL VOLTAGE  
115/230V OUTPUT  
220/240V INPUT  
50/60HZ

## Flex Outlets (NON UK)

## Plateswitches

SP  
2 WAY  
10 AMP



### FINISHES

|                         |          |   |          |   |         |   |          |   |          |   |
|-------------------------|----------|---|----------|---|---------|---|----------|---|----------|---|
| BRUSHED STAINLESS STEEL | K5261BSS | 1 | K5114BSS | 1 | K703BSS | 1 | K2240BSS | 1 | K4671BSS | 5 |
| BRUSHED CHROME          | K5261BRC | 1 | K5114BRC | 1 | K703BRC | 1 | K2240BRC | 1 | K4671BRC | 1 |
| SATIN GOLD              | K5261SAG | 1 | K5114SAG | 1 | K703SAG | 1 |          |   | K4671SAG | 1 |
| POLISHED CHROME         | K5261PCR | 1 | K5114PCR | 1 | K703PCR | 1 |          |   | K4671PCR | 1 |

**LEAD TIMES**  
Please contact our Customer  
Services Department on  
01268 563 404

**MOUNTING BOXES**  
**FLUSH**  
886ZIC  
(Up to 6mm<sup>2</sup> conductor)  
878ZIC  
(Up to 10mm<sup>2</sup> conductor)  
Rotary operated shutter.  
**DIMENSIONS**  
86 x 146mm  
**FIXING CENTRES**  
120.6mm  
BS 4177:1992

**MOUNTING BOX**  
**FLUSH**  
878ZIC  
This product is rated at  
440 volts with a motor load  
rating of up to 12kW – 16 HP  
at 415V 3 phase.  
It has a utilisation category of  
AC22A – switching of mixed  
resistive and inductive loads  
including moderate overloads  
for a continuous duty of 32  
amps. Making capacity is 2000  
amps peak.  
**TERMINAL CAPACITY**  
16mm<sup>2</sup> conductors.  
**DIMENSIONS**  
146 x 86mm  
BS EN 60947-3:1992

**MOUNTING BOXES**  
**FLUSH**  
878ZIC  
This design incorporates a  
double wound isolating  
transformer rated 20VA at 230  
or 115 volts and meets  
BS EN 61558-2-5:1998  
making it safe for use in  
bathrooms.  
Insertion of a shaver/  
toothbrush plug automatically  
switches on by energising the  
primary side of the isolating  
transformer – removal  
automatically switches  
off. The transformer is  
protected against overload  
by an automatic solid state  
overload device with automatic  
resetting.  
**DIMENSIONS**  
146 x 86mm  
**FIXING CENTRES**  
120.6mm  
BS EN 61558-2-5:1998

**MOUNTING BOXES**  
**FLUSH**  
866ZIC  
**SURFACE**  
**WITH KNOCKOUTS**  
K899ALM  
**SURFACE WITHOUT**  
**KNOCKOUTS**  
K829ALM  
**CABLE DIAMETER**  
Minimum 4mm  
Maximum 14.5mm  
**DIMENSIONS**  
1 gang: 86 x 86mm  
**FIXING CENTRES**  
1 gang: 60.3mm  
BS 5733:2010

**MOUNTING BOXES**  
**FLUSH**  
3995ZIC  
**SURFACE**  
**WITH KNOCKOUTS**  
K899ALM  
**SURFACE WITHOUT**  
**KNOCKOUTS**  
K829ALM  
These switches do not have  
to be derated when used with  
fluorescent or inductive loads.  
Switches can be wired as  
either one-way or two-way.  
**DIMENSIONS**  
86 x 86mm  
**FIXING CENTRES**  
60.3mm  
BS EN 60669-1:1999  
If an intermediate switch is  
required, a modular (Grid Plus)  
version is available. Order  
K3431 grid plate, K3701 grid  
frame and K4893WHI 20A  
intermediate switch