



Technical Hotline
+44 (0)1268 563720

Albany Plus™

3 Pole Fan Isolator

2 GANG SP
2 WAY
10 AMP

3 GANG SP
2 WAY
10 AMP

1 GANG SP
2 WAY
WIDE ROCKER
10 AMP

2 GANG SP
2 WAY
WIDE ROCKER
10 AMP

WITHOUT
SWITCHLOCK
10 AMP

SWITCHLOCK
FOR FAN
ISOLATOR



K4672BSS	1	K4673BSS	5	K4761BSS	5	K4762BSS	5	K4860BSS	1	K4858	10
K4672BRC	1	K4673BRC	1	K4761BRC	1	K4762BRC	1	K4860BRC	1		
K4672SAG	1	K4673SAG	1	K4761SAG	1	K4762SAG	1	K4860SAG	1		
K4672PCR	1	K4673PCR	1	K4761PCR	1	K4762PCR	1	K4860PCR	1		

MOUNTING BOXES
FLUSH
3995ZIC
SURFACE
WITH KNOCKOUTS
K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
These switches do not have to be derated when used with fluorescent or inductive loads. Switches can be wired as either one-way or two-way.
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS EN 60669-1:1999
If an intermediate switch is required, a modular (Grid Plus) version is available. Order K3431 grid plate, K3701 grid frame and K4893WHI 20A intermediate switch

MOUNTING BOXES
FLUSH
3995ZIC
SURFACE
WITH KNOCKOUTS
K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
These switches do not have to be derated when used with fluorescent or inductive loads. Switches can be wired as either one-way or two-way.
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS EN 60669-1:1999
If an intermediate switch is required, a modular (Grid Plus) version is available. Order K3431 grid plate, K3701 grid frame and K4893WHI 20A intermediate switch

MOUNTING BOXES
FLUSH
3995ZIC
SURFACE
WITH KNOCKOUTS
K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
These switches do not have to be derated when used with fluorescent or inductive loads. Switches can be wired as either one-way or two-way.
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS EN 60669-1:1999
If an intermediate switch is required, a modular (Grid Plus) version is available. Order K3431 grid plate, K3701 grid frame and K4893WHI 20A intermediate switch

MOUNTING BOXES
FLUSH
3995ZIC
SURFACE
WITH KNOCKOUTS
K899ALM
SURFACE WITHOUT
KNOCKOUTS
K829ALM
These switches do not have to be derated when used with fluorescent or inductive loads. Switches can be wired as either one-way or two-way.
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS EN 60669-1:1999
If an intermediate switch is required, a modular (Grid Plus) version is available. Order K3431 grid plate, K3701 grid frame and K4893WHI 20A intermediate switch

MOUNTING BOXES
FLUSH
3995ZIC
SURFACE
WITH KNOCKOUTS
K2160WHI
For local isolation of fans with or without timers for repair or routine maintenance.
DIMENSIONS
86 x 86mm
FIXING CENTRES
60.3mm
BS EN 60669-2-4

For use with K4860