

## Features and Benefits



A screwless cord grip automatically clamps and securely holds the cable in connection units with base and front flex outlets



Switched units are double pole with neutral pole contacts 'making' before and 'breaking' after live contacts. Rockers with built-in indicators are available



When servicing or repairing appliances, fuse carriers remain attached to the frontplate when opened and can be padlocked for safety




An optional tamperproof screw on fuse carriers is particularly useful for appliances in public areas



In-line terminals, backed out captive terminal screws and clear marking make installation easy

## Connection Units

### SWITCHED 13 AMP



**K330WHI** 10  
**K330GRA** 10  
DP WITH FLEX OUTLET IN BASE AND THICK FRONTPLATE

**K370WHI** 10  
**K370GRA** 10  
DP WITH NEON, FLEX OUTLET IN BASE AND THICK FRONTPLATE

**K370D1WHI** 10  
DP WITH NEON, FLEX OUTLET IN BASE, THICK FRONTPLATE AND RED ROCKER

**K1030WHI** 10  
DP WITH FRONT FLEX OUTLET

**MOUNTING BOXES**  
**K1030, K1040, K1060 and K1070**  
FLUSH  
866ZIC (35mm)  
**SURFACE**  
K2031WHI

**K330, K385 and K370**  
FLUSH  
866ZIC (35mm)  
**SURFACE**  
K2140WHI

All units are fitted with a 13A fuse-link to BS 1362. See page 222 for spare fuse-links.

The fuse carrier can be locked in the open position by removing the fuse and using K2000 fuse carrier padlock



**K385WHI** 10  
13A RCD CONNECTION UNIT 30mA PASSIVE AND THICK FRONTPLATE

**K1040WHI** 10  
DP  
**K1040KOWHI** 10  
DP WITH TAMPERPROOF SCREW

**K1060WHI** 10  
DP WITH NEON  
**K1060D1WHI** 10  
DP WITH NEON AND RED ROCKER

**K1070WHI** 10  
DP WITH FRONT FLEX OUTLET AND NEON  
**K1070D1WHI** 10  
DP WITH FRONT FLEX OUTLET, NEON AND RED ROCKER

**K2000** 1  
PADLOCK

**K1030 and K1070** front flex outlet products cannot be mounted directly onto M1 Cable Box K2131WHI. A mounting frame K2134WHI will have to be used between the product and the box.

Base entry frontplates are 12.5mm deep.

**DIMENSIONS**  
86 x 86mm  
**FIXING CENTRES**  
60.3mm  
BS 1363 Pt 4:1995

### UNSWITCHED 13 AMP



**K337WHI** 10  
WITH FLEX OUTLET IN BASE AND THICK FRONTPLATE

**K337KOWHI** 10  
WITH FLEX OUTLET IN BASE, THICK FRONTPLATE AND TAMPERPROOF SCREW FOR FUSE CARRIER

**K377WHI** 10  
WITH FLEX OUTLET IN BASE, NEON AND THICK FRONTPLATE

**MOUNTING BOXES:**  
FLUSH  
866ZIC (35mm)  
**SURFACE**  
K2140WHI

All units are fitted with a 13A fuse-link to BS 1362. See page 222 for spare fuse-links.

Base entry frontplates are 12.5mm deep. The fuse carrier can be locked in the open position by removing the fuse and using K2000 fuse carrier padlock.

**DIMENSIONS**  
86 x 86mm  
**FIXING CENTRES**  
60.3mm  
BS 1363 Pt 4:1995  
**K1040KO AND K337KO**  
Key (3405ZIC) is supplied