

## Blank Plates


Flex Outlet  
FrontplateEuro Modular  
FrontplatesEuro Power  
Modules

20 AMP



K3825WHI

K3827WHI



K3828WHI



K5033WHI




K1090WHI



K181WHI



K182WHI



K184WHI



K5830WHI



K5831WHI



K5832WHI



K5833WHI



K5834WHI



K5837WHI

- K3825WHI** 10  
1 GANG MOULDED  
ARCHITRAVE
- K3827WHI** 10  
1 GANG MOULDED
- K3828WHI** 10  
2 GANG MOULDED
- K5033WHI** 1  
METAL

**K3825WHI**  
For use with 3921ZIC and K2151WHI  
MOUNTING BOXES.

**K5033WHI**  
For use with 5120ALM deep metal box.

**DIMENSIONS**  
K3825WHI: 86 x 31mm  
K3827WHI: 86 x 86mm  
K3828WHI: 86 x 146mm  
K5033WHI: 178 x 165mm

**FIXING CENTRES**  
K3825WHI: 60.3mm  
K3827WHI: 60.3mm  
K3828WHI: 120.6mm  
K5033WHI: 133mm  
BS 5733:2010

- K1090WHI** 10  
FLEX OUTLET FRONTPLATE  
UNFUSED

Complete with three pairs of terminals, each suitable for 2 x 2.5mm<sup>2</sup> conductors and a 1.5mm<sup>2</sup> flexible cord. A cord-grip is also fitted.

Frontplate thickness is 12.5mm.

Cable entry diameter is 11mm.

**DIMENSIONS**  
86 x 86mm  
**FIXING CENTRES**  
60.3mm

BS EN 60670-22:2006

- K181WHI** 10  
1 GANG EURO FRONTPLATE  
ONE MODULE  
APERTURE SIZE 25 X 50MM

- K182WHI** 10

- K182GRA** 10

- 1 GANG EURO FRONTPLATE  
TWO MODULE  
APERTURE SIZE 50 X 50MM

- K184WHI** 10

- K184GRA** 10

- 2 GANG EURO FRONTPLATE  
FOUR MODULE  
APERTURE SIZE 100 X 50MM

- K185WHI** 10

- 3 GANG EURO FRONTPLATE  
SIX MODULE  
APERTURE SIZE 150 X 50MM

**MOUNTING BOXES**

Suitable for flush boxes to BS 4662:2006 and surface boxes to BS 5733:2010 Refer to appropriate module for minimum box depth.

**K185WHI MOUNTING BOX**  
35mm VTS8035 (For use with Pinnacle and Premier cable management systems) K2153WHI 30mm

**FIXING CENTRES**  
1 GANG: 60.3mm 2 GANG: 120.6mm  
BS 5733:2010 where applicable  
Note: No grid required, modules just clip into place

- K5830WHI** 1  
**K5830BLK** 1  
UK 1 GANG EURO 2 MODULE  
13A 250V SHUTTERED

- K5831WHI** 10

- K5831BLK** 10

- GERMAN 2P+E  
16A 250V SHUTTERED  
EURO 2 MODULE (NON UK)

- K5832WHI** 10

- K5832BLK** 10

- AMERICAN 2P+E  
15A 127V SHUTTERED  
EURO 2 MODULE (NON UK)

**K5830 MOUNTING BOX**  
35mm minimum  
46mm (for extra wiring space)

**DIMENSIONS**  
50 x 50mm  
BS 1363 Pt2:1995

**K5831 MOUNTING BOX**  
46mm

**DIMENSIONS**  
50 x 50mm  
IEC 60884-1:2006

**K5832 MOUNTING BOX**  
35mm

46mm (for extra wiring space)

**DIMENSIONS**  
50 x 50mm

SASO 2204:2003

- K5833WHI** 10  
**K5833BLK** 10  
UK 1 GANG EURO 2 MODULE  
5A 250V SHUTTERED

- K5834WHI** 10

- K5834BLK** 10

- FRENCH/BELGIAN 2P+E  
16A 250V SHUTTERED  
EURO 2 MODULE (NON UK)

- K5837WHI** 1

- K5837BLK** 1

- USB CHARGING MODULE  
EURO 2 MODULE

**K5833 MOUNTING BOX**  
35mm minimum  
46mm (for extra wiring space)

**DIMENSIONS**  
50 x 50mm  
BS 546:1950

**K5834 MOUNTING BOX**  
46mm

**DIMENSIONS**  
50 x 50mm  
NF C61-314

**K5837 MOUNTING BOX**  
35mm, 46mm (for extra wiring space)

**DIMENSIONS**  
50 x 50mm

USB charging sockets, each capable of supporting 2A charge (total of 2A).

IEC 60950-1  
IEC 61000-6-1/3