

Masterseal Plus™

mkelectric.co.uk



Key Operated Switches

20 AMP
IP66



K56425GRY



K56425WHI



K56425BLK

Connection Units

13 AMP
IP66



K56410WHI



K56410BLK



K56410GRY

Switches

10 AMP
IP66



K56400GRY



K56401WHI



K56402BLK

10 AMP
IP66



K56406GRY



K56407BLK



K56408WHI

20 AMP
IP66



K56409GRY



K56409WHI



K56409BLK

Grid Plus Enclosures

IP56



K56414GRY



K56414WHI



K56414BLK

K56425GRY 1
K56425WHI 1
K56425BLK 1
20A
1 GANG
DP KEY OPERATED SWITCH

Fixing holes are for No.8 woodscrews (not supplied).
K56425 Backbox has 4 x 20mm entries, 1 on top, bottom and each side and is supplied with an earth terminal in the back box.
DIMENSIONS
160 x 117 x 89mm
BS EN 60669-1:1999
IP66 BS EN 60529:1992

K56410GRY 1
K56410WHI 1
K56410BLK 1
13A DP
1 GANG
SWITCHED, FUSED

Fitted with a 13A fuse link to BS 1362.
Fixing holes are for No.8 woodscrews (not supplied).
Backbox has 4 x 20mm entries, 1 on each edge, and is supplied with an earth terminal in the backbox.
DIMENSIONS
160 x 117 x 89mm
BS 1363-4:1995
IP66 BS EN 60529:1992

K56400GRY 1
K56400WHI 1
K56400BLK 1
10A 1 GANG
SP ONE-WAY
K56401GRY 1
K56401WHI 1
K56401BLK 1
10A 1 GANG
SP TWO-WAY
K56402GRY 1
K56402WHI 1
K56402BLK 1
10A 2 GANG
SP ONE-WAY

K56406GRY 1
K56406WHI 1
K56406BLK 1
10A 1 GANG
DP ONE-WAY
K56407GRY 1
K56407WHI 1
K56407BLK 1
10A 1 GANG
SP TWO-WAY
PUSH TO MAKE OR
PUSH TO BREAK
'BELL'
K56408GRY 1
K56408WHI 1
K56408BLK 1
10A 1 GANG
SP TWO-WAY
PUSH TO MAKE OR
PUSH TO BREAK
'PRESS'

K56409GRY 1
K56409WHI 1
K56409BLK 1
20A 1 GANG
DP ONE-WAY
'PRESS'

Fixing holes are for No.8 woodscrews (not supplied).
Each switch is fitted with a neon which can be wired as a locator.
The enclosure has 4 x 20mm entries, 1 on top, bottom and each side and is supplied with an earth terminal and a loop terminal in the back box.
DIMENSIONS
95 x 95 x 57mm
BS EN 60669-1:1999
IP66 to BS EN 60529:1992

K56414GRY 1
K56414WHI 1
K56414BLK 1
MODULAR GRID PLUS ENCLOSURE SUPPLIED WITH 1 AND 2 GANG INSERTS*

Fixing holes are for No.8 woodscrews (not supplied).
Backbox has 4 x 20mm entries, 1 on top, bottom and each side. Supplied with an earth terminal and a loop terminal in the backbox.
DIMENSIONS
95 x 95 x 80mm
BS EN 60669-1:1999
IP56 to BS EN 60529:1992

Fixing holes are for No.8 woodscrews (not supplied).
Each switch is fitted with a neon which can be wired as a locator.
The enclosure has 4 x 20mm entries, 1 on top, bottom and each side and is supplied with an earth terminal and a loop terminal in the back box.
These switches (except push switches) do NOT have to be derated when used with fluorescent or inductive loads.
DIMENSIONS
95 x 95 x 57mm
BS EN 60669-1:1999
IP66 to BS EN 60529:1992

* NOTE: Installers may select any switch or neon modules, excluding dimmers, from Grid Plus range and configure product to suit installation requirements.