



Technical Hotline
+44 (0)1268 563720

Logic Plus™

WIRING DEVICES
WHITE

Intelligent LED Dimmer Switch

220V TO 240V A.C. 50HZ
LED, TUNGSTEN FILAMENT
AND LOW VOLTAGE
HALOGEN LIGHTING

Intelligent Dimmer Switches

230V A.C. 50HZ
TUNGSTEN FILAMENT
AND LOW VOLTAGE
HALOGEN LIGHTING

Standard Dimmer Switches

230V A.C. 50HZ
TUNGSTEN FILAMENT

Dimmer Switches (NON UK)

200-250V A.C.
50 OR 60HZ



K1523WHILV



K1524WHILV



K1501WHILV



K1521WHILV



K1522WHILV



K1511WHI



K1531WHI



K1532WHI



K1533WHI



K1541WHI



K1561WHI



K1661WHI



4053PLWHIT9

K1523WHILV

1 GANG SINGLE
2 WAY
40W/VA - 300W/240VA
LED: 4-70W

K1524WHILV

1 GANG DOUBLE
2 WAY
40W/VA - 300W/240VA
LED: 4-70W

MOUNTING BOXES

FLUSH
861ZIC – 25mm deep min

SURFACE

K2140WHI – 30mm deep
Micro controller based circuitry to provide electronic soft-start and overload protection. Suitable for use with most major manufacturers LED lamps or electronic / wire wound transformers. Can also be used with good quality mains voltage GU10 halogen lamps.

Do not mix load types
This dimmer offers the user the ability to adjust the minimum brightness level.

Max number of lamps (10)

DIMENSIONS
86 x 86mm

FIXING CENTRES
60.3mm
BS EN 60669-2-1

K1501WHILV

1 GANG SINGLE
TWO WAY 60W/VA-500W/400 VA

K1521WHILV

1 GANG SINGLE
TWO WAY 40W/VA-300W/240 VA

K1522WHILV

1 GANG DOUBLE
TWO WAY 2 X 40W/VA-300W/240 VA

FLUSH

861ZIC/866ZIC

SURFACE

K2140WHI

Micro controller based circuitry to provide electronic soft-start and overload protection. Suitable for use with good quality electronic or wire wound transformers. Can also be used with good quality mains voltage halogen lamps incorporating GU10 bases. Please check with lamp manufacturer to determine suitability.

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

Conforms to BS EN 60669-2-1

K1511WHI

1 GANG SINGLE
ONE WAY 65-450W

K1531WHI

1 GANG SINGLE
ONE WAY 40-250W

K1532WHI

1 GANG DOUBLE
ONE WAY 2 X 40-250W

K1533WHI

1 GANG DOUBLE
TWO WAY 2 X 40-250W

K1534WHI

1 GANG SINGLE
TWO WAY 40-250W

K1535WHI

1 GANG SINGLE
TWO WAY 65-450W

MOUNTING BOXES

FLUSH
861ZIC/866ZIC

SURFACE

K2140WHI

Not suitable for fluorescent lamps or low voltage lighting.

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

Conforms to BS EN 60669-2-1

K1541WHI

1 GANG SINGLE
ONE WAY
75-500W 50HZ

K1561WHI

1 GANG SINGLE
TWO WAY
100-1000W 50HZ

K1641WHI

1 GANG SINGLE
ONE WAY
75-500W 60HZ

K1661WHI

1 GANG SINGLE
TWO WAY
100-1000W 60HZ

MOUNTING BOXES

FLUSH
861ZIC/866ZIC

SURFACE

K2140WHI

PATRESS

For mounting in 16mm deep boxes a mounting frame 40533PLWHIT9 is available.

DIMENSIONS

86 x 86mm

FIXING CENTRES

60.3mm

40533PLWHIT9

CAN BE USED WITH
LOGIC PLUS DIMMERS TO
STAND PRODUCT FROM
MOUNTING SURFACE
WHERE BACK BOX DEPTH
IS NOT SUFFICIENT

DIMENSIONS

86 x 86mm

Patress thickness is 5mm

FIXING CENTRES

60.3mm