

RKDG D17 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Intelligent cabling solutions can save you valuable time and money.**

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the seal possible

seal possible

General ordering data

Version	FieldPower®, Field Power® sealing insert, round, IP65, 15 - 17 mm
Order No.	4324010000
Type	RKDG D17 PT6
GTIN (EAN)	4032248641284
Qty.	10 pc(s).

Creation date May 2, 2022 9:17:30 AM CEST

Catalogue status 22.04.2022 / We reserve the right to make technical changes.

RKDG D17 PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	18 mm	Depth (inches)	0.709 inch
Height	33.8 mm	Height (inches)	1.331 inch
Width	46.7 mm	Width (inches)	1.839 inch
Net weight	22.8 g		

Temperatures

Operating temperature	-40 °C...85 °C
-----------------------	----------------

General data

Clamping range, max.	17 mm	Clamping range, min.	15 mm
Colour	black	Design	Foldable seal
Line type	round	Material	EPDM
Mounting position, installation notice	in FieldPower® sealing slot	Protection degree	IP65
Silicone	No	UL 94 flammability rating	HB

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ECLASS 9.1	27-18-27-90
ECLASS 10.0	27-18-28-15	ECLASS 11.0	27-18-28-15

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	UL Certificate FieldPower® Box and accessories
Engineering Data	CAD data – STEP
Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format