

Mini vibration motor 2.0mm – 316040001



This mini vibration motor worked at 3V can be used for multipurpose.

Technical details

Dimensions	0mm x0mm x0mm
Weight	G.W 2g
Battery	Exclude

Part List

Mini vibration motor	1
----------------------	---

1. Construction Form

No.	ITEM	Contents
1-1	Motor Construction	Φ10-Flat <u>Coreless</u> Vibration Motor
1-2	Coil Construction	Flat <u>Coreless</u> Coil
1-3	Rectifying Method	Precious Brush and Commutator

2. Standard Operating Condition

No.	ITEM	Contents
2-1	Rated Voltage	DC 3.0V
2-2	Rated Load	Vibration Weight
2-3	Rotation Direction	CCW or CW
2-4	Motor Position	Any Position Available
2-5	Voltage Range for Use	DC 2.5~3.5V
2-6	Allowable Temperature Range	Working Temperature: -20°C-70°C
2-7	Storage Environment	-30°C-80°C

Add: Measuring Condition

1. Measuring Temperature: 25 ± 2
- 2.2. Measuring Relative Humidity: 45-75%RH