

## Product information

# 11 12 160

## Insulation Stripper

Universal

- For single, multiple and fine stranded conductors with plastic or rubber insulation up to Ø 5.0 mm or 10 mm<sup>2</sup>
- Easy adjustment to the required diameter of solid or stranded wire with knurled screw and lock nut
- Special tool steel, forged, oil-hardened



### General

Article No.	11 12 160
EAN	4003773034964
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	156 g
Dimensions	160 x 57 x 19 mm
Reach	no
RohS	no

### Technical details

Stripping capacities in square millimetres	10 mm <sup>2</sup>
Stripping capacities (diameter)	Ø 5.0 mm
AWG	8

### Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111510

### Spare Parts

11 09 01	Set of spare parts (screw and nut) for 11 XX 160,
----------	---

*technical change and errors excepted*