

Product information

12 52 195

KNIPEX PreciStrip16 Automatic Insulation Stripper






Properly stripped away: with deft precision, strip everything from very fine to thick cables with stranded or solid conductors


- Simple, precise stripping of fine wires and solid round cables with a wide capacity range from 0.08 to 16 mm² with only one pair of pliers
- Good grip provided by semi-circular grooved metal holding clamps; exact cut thanks to parabolic stripping blade
- A patented automatism regulates the depth of the cut; the neutral point of the automatism can be adjusted in fine steps in special operating conditions (insulation material, temperature)
- With adjustable length stop for precision work repeated accurately each time
- Inscription area for customisation
- Comfortable operation with ergonomic dual-component handle
- With tether attachment point, suitable for KNIPEX Tethered Tools accessories
- Easily replaceable blade cassette




General	
Article No.	12 52 195
EAN	4003773085829
Weight	180 g
Dimensions	195 x 120 x 28 mm
Reach	no
RohS	no
Technical details	
Stripping capacities in square millimetres	0.08 — 16.0 mm ²
AWG	28 — 6
Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
Spare Parts	
12 49 23	Spare length stop for 12 42 / 52 195,
12 49 32	Spare knife block with special knives for 12 52 195,
12 49 31	Spare blades block for 12 52 195,

technical change and errors excepted







Semi-circular grooved holding clamp for better grip that holds practically any insulation material securely in place



For special requirements, such as particularly hard or soft insulation materials, optimum fine adjustments can be made using the adjusting wheel with its tactile locking positions



With cable cutter on the top side for up to 16 mm²