

## Product information

**22 02 160**


- For bending wire loops
- Round, short jaws; finely ground
- Smooth tips
- Special tool steel, forged, oil-hardened

## Round Nose Pliers

DIN ISO 5745



General	
Article No.	22 02 160
EAN	4003773023173
Pliers	black atramentized
Head	polished
Handles	with multi-component grips
Weight	170 g
Dimensions	160 x 57 x 19 mm
Standard	DIN ISO 5745
Reach	no
RohS	no
Technical details	
Jaw thickness (joint) (T1)	9.5 mm
Tips thickness (T2)	3.0 mm
Jaw length (L3)	30.0 mm
Head width (W3)	18 mm



Classification	
eCl@ss 5.1.4	21040301
ETIM 5.0	EC000834
ETIM 6.0	EC000834
proficl@ss 6.0	AAA005c004
UNSPSC 13.1	27112125

*technical change and errors excepted*

