

## Product information

# 25 02 160

## Snipe Nose Side Cutting Pliers (Radio Pliers)

DIN ISO 5745

- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 61 HRC
- Straight jaws
- Vanadium electric steel, forged, multi stage oil-hardened




### General

|             |                            |
|-------------|----------------------------|
| Article No. | 25 02 160                  |
| EAN         | 4003773023166              |
| Pliers      | black atramentized         |
| Head        | polished                   |
| Handles     | with multi-component grips |
| Weight      | 144 g                      |
| Dimensions  | 160 x 55 x 19 mm           |
| Standard    | DIN ISO 5745               |
| Reach       | no                         |
| RohS        | no                         |

### Technical details

|  |          |
|--|----------|
| Cutting capacities medium hard wire (diameter) | Ø 2.5 mm |
| Cutting capacities hard wire (diameter)        | Ø 1.6 mm |
| Jaw thickness (joint) (T1)                     | 9.0 mm   |
| Tips width (W4)                                | 3.0 mm   |
| Tips thickness (T2)                            | 2.5 mm   |
| Jaw length (L3)                                | 50.0 mm  |
| Head width (W3)                                | 16.5 mm  |



| Classification |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040301   |
| proficl@ss 6.0 | AAA004c004 |
| UNSPSC 13.1    | 27112134   |

*technical change and errors excepted*

