

## Product information

# 61 02 200

## Bolt End Cutting Nipper

High lever transmission

DIN ISO 5743

- Powerful, compact, comfortable
- With slim multi-component grips without collar for better handling and easier transport
- With large contact surface on the handles for better allotment of pressure and more comfort at work
- Particularly high cutting capacity with minimum effort due to optimum transmission ratio
- Handles angled for better accessibility
- Vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	61 02 200
EAN	4003773067047
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	435 g
Dimensions	200 x 45 x 15 mm
Standard	DIN ISO 5743
Reach	no
RohS	no
Technical details	
Cutting capacities soft wire (diameter)	Ø 1 – 6 mm
Cutting capacities medium hard wire (diameter)	Ø 4.0 mm
Cutting capacities hard wire (diameter)	Ø 3.5 mm
Cutting capacities piano wire (diameter)	Ø 3.0 mm
Classification	
eCl@ss 5.1.4	21040302
ETIM 5.0	EC002222
ETIM 6.0	EC002222
proficl@ss 6.0	AAA947c004
UNSPSC 13.1	27112117

technical change and errors excepted

