

## Product information

# 71 22 200

## KNIPEX CoBolt®

### Compact Bolt Cutter



MM   $\angle 20^\circ$



#### Clever muscle man

- With slim multi-component grips without collar for better handling and easier transport
- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- With precision cutting edges for soft, hard and piano wire
- Cuts bolts, nails, rivets, etc. up to  $\varnothing$  5.2 mm
- Efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- 20° angled head with joint bar on one side and side cutter for almost flush cutting, with space for gripping
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened

### General

|             |                                 |
|-------------|---------------------------------|
| Article No. | 71 22 200                       |
| EAN         | 4003773066873                   |
| Pliers      | black atramentized              |
| Handles     | with slim multi-component grips |
| Weight      | 375 g                           |
| Dimensions  | 200 x 62 x 24 mm                |
| Reach       | yes                             |
| RohS        | no                              |

### Technical details

|  |                      |
|--|----------------------|
| Cutting capacities soft wire (diameter)        | $\varnothing$ 6 mm   |
| Cutting capacities medium hard wire (diameter) | $\varnothing$ 5.2 mm |
| Cutting capacities hard wire (diameter)        | $\varnothing$ 4.0 mm |
| Cutting capacities piano wire (diameter)       | $\varnothing$ 3.6 mm |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040302   |
| ETIM 5.0       | EC002689   |
| ETIM 6.0       | EC002689   |
| proficl@ss 6.0 | AAC440c002 |
| UNSPSC 13.1    | 27111512   |

### Spare Parts

|           |                |
|-----------|----------------|
| 71 19 200 | Buffer spring, |
|-----------|----------------|

technical change and errors excepted



20° angled head with single-sided joint bar and diagonal cutting edge for flush cutting; with space for gripping

