

Product information

85 01 250

KNIPEX SmartGrip®

Water Pump Pliers with automatic adjustment

DIN ISO 8976



- Ideal for frequent changeovers to workpieces of different sizes
- Automatic adjustment per one-hand operation both for right-handed and left-handed use
- Good access to the workpiece thanks to the slim dimensions of head and joint area and flush joint bolt
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Pinch guard prevents operators' fingers being pinched
- Locking lever for space-saving transport with reliable closed handles
- Chrome vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	85 01 250
EAN	4003773061304
Pliers	grey atramentized
Head	polished
Handles	with non-slip plastic coating
Weight	370 g
Dimensions	250 x 48 x 13 mm
Standard	DIN ISO 8976
Reach	no
RohS	no

Technical details

Capacities for pipes (diameter)	Ø 1 1/4
Capacities for pipes (diameter)	Ø 32 mm
Capacities for nuts	36 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000164
ETIM 6.0	EC000164
proficl@ss 6.0	AAA936c004
UNSPSC 13.1	27112112

technical change and errors excepted



