

Product information

86 03 400

Pliers Wrench XL

Pliers and a wrench in a single tool



- The unique installation tool now also in 400 mm length
- For opening widths up to 85 mm / 3 3/8"
- Also excellent for gripping, holding, pressing and bending workpieces
- Optimised adjustment to the workpiece with hand-friendly position of grips
- Reliable catching of the hinge bolt: no unintentional shifting
- Lever transmission greater than 10 : 1 for strong gripping power
- Adjustable tightening tool
- Replaces diverse expensive, large open-end wrenches up to AF 85 mm or 3 3/8"
- Parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- Smooth jaws, for damage free installation of quality union joints made from brass, red brass or stainless steel
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Push the button for adjustment on the workpiece
- Chrome vanadium electric steel, forged, oil-hardened




General

Article No.	86 03 400
EAN	4003773077312
Pliers	chrome-plated
Head	chrome-plated
Handles	plastic coated
Weight	1,460 g
Dimensions	400 x 81 x 23 mm
Reach	no
RohS	no

Technical details

Jaw thickness (joint) (B2)	16.0 mm
Joint thickness (B3)	20.0 mm
Tips thickness (B1)	12.5 mm
Adjustment positions	25
Capacities for nuts	Ø 3 3/8 Inch
Capacities for nuts	85 mm



Classification

eCl@ss 5.1.4	21043826
proficl@ss 6.0	EAA961c002
UNSPSC 13.1	27112112

Spare Parts

87 09 400	Range of spare parts adjustment for 87 400,
-----------	---

technical change and errors excepted

