

Product information

90 22 10 BK

KNIPEX BiX®

Cutters for plastic pipes and sealing sleeves



Clean cut everytime

Compact. Versatile. Fast.

Practical tool for plumbers and electricians: Cuts plastic pipes and sealing sleeves quickly and efficiently

- Clever pipe cutter: Cuts pipes without shavings and fits comfortably in the hand
- Can cut high-temperature plastic drain pipes and electrical conduits in next to no time
- Can be used to cut sealing sleeves during final assembly – close to the wall, standard-compliant
- Cuts unreinforced plastic pipes from Ø 20 to 50 mm with a wall thickness of up to 2.4 mm
- Cuts pipes quickly, cleanly and without shavings
- Cuts sealing sleeves approx. 2-3 mm from the wall
- Rotatable knife block for cutting plastic pipes (blade in the middle) and sealing sleeves (blade outside)
- With locking mechanism for safe transport
- Two spare blades integrated in the tool
- Tool made of stable, reinforced plastic, die-cast zinc blade unit
- Blades made of special surgical stainless steel – Made in Solingen

General

Article No.	90 22 10 BK
EAN	4003773087311
Weight	108 g
Dimensions	72 x 50 x 40 mm
Reach	no
RohS	no

Technical details

	Ø 20 – 50 mm
	Ø 20 – 50 mm

Classification

eCl@ss 5.1.4	21040601
ETIM 5.0	EC000148
ETIM 6.0	EC000148
proficl@ss 6.0	AAB927c006

Spare Parts

90 22 10 E01	Spare blades for 90 22 10 BK,
--------------	-------------------------------

technical change and errors excepted











