

Product information

97 90 06

Crimp Assortment

For wire ferrules

DIN 46228-4: 2020-03

- With crimping pliers for wire ferrules 97 71 180
- Wire ferrules with plastic collar
- In a TANOS MINI-systainer® (solid plastic box)
- T-Loc fastener for one-handed operation: open or close the systainer® with one turn and connect to a second systainer®
- Opening when connected: fast and simple access to content without disconnecting
- Two stackable plastic inserts with 6 trays each for connectors
- With an assortment of wire ferrules with/without collar




General

Article No.	97 90 06
EAN	4003773025542
Weight	1,000 g
Dimensions	170 x 68 mm
Standard	DIN 46228-4: 2020-03
Reach	no
RohS	no

Classification

eCl@ss 5.1.4	27400218
ETIM 5.0	EC000524
ETIM 6.0	EC000524
proficl@ss 6.0	EAB559c013
UNSPSC 13.1	27112147

Content

97 71 180	1 x Crimping Pliers for wire ferrules (0,25 – 16 mm ²) 
	40 x Wire ferrules with plastic collar 14 / 8 mm (0,5 mm ²)
	50 x Wire ferrules with plastic collar 14 / 8 mm (0,75 mm ²)
	75 x Wire ferrules with plastic collar 14 / 8 mm (1 mm ²)
	75 x Wire ferrules with plastic collar 14 / 8 mm (1,5 mm ²)
	150 x Wire ferrules with plastic collar 14 / 8 mm (2,5 mm ²)
	200 x Wire ferrules with plastic collar 17 / 10 mm (4 mm ²)
	200 x Wire ferrules with plastic collar 20 / 12 mm (6 mm ²)

Content

	200 x Wire ferrules with plastic collar 22 / 12 mm (10 mm ²)
	200 x Wire ferrules with plastic collar 24 / 12 mm (16 mm ²)

technical change and errors excepted

Systemer® is a registered trademark of TANOS GmbH

