

## Product information

# 98 20 25

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

## Screwdrivers for slotted screws

IEC 60900 DIN EN 60900



⚡ 1000 V ⚡

### General

Article No.	98 20 25
EAN	4003773062325
point	burnished
Handles	insulating multi-component handle, VDE-tested
Weight	32 g
Dimensions	177 x 24 x 24 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

### Technical details

Blade length	75 mm
Length of non-insulated blade	15 mm
Handle length	102 mm
Blade width	2.5 mm
Blade thickness	0.4 mm
VDE tested	yes

### Classification

eCl@ss 5.1.4	21040401
ETIM 5.0	EC000158
ETIM 6.0	EC000158
proficl@ss 6.0	AAA817c008
UNSPSC 13.1	27111701

*technical change and errors excepted*