

Product information

98 21 45

Screwdrivers for slotted screws

IEC 60900 DIN EN 60900

- Especially for meter assembly with blade length of 180 mm
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000V ⚡

| General | |
|-------------|---|
| Article No. | 98 21 45 |
| EAN | 4003773026426 |
| point | burnished |
| Handles | insulating multi-component handle, VDE-tested |
| Weight | 66 g |
| Dimensions | 287 x 28 x 29 mm |
| Standard | DIN EN 60900 IEC 60900 |
| Reach | no |
| RohS | no |

| Technical details | |
|-------------------------------|--------|
| Blade length | 180 mm |
| Length of non-insulated blade | 15 mm |
| Handle length | 107 mm |
| Blade width | 4.5 mm |
| Blade thickness | 0.8 mm |
| VDE tested | yes |

| Classification | |
|----------------|------------|
| eCl@ss 5.1.4 | 21040401 |
| ETIM 5.0 | EC000158 |
| ETIM 6.0 | EC000158 |
| proficl@ss 6.0 | AAA817c008 |
| UNSPSC 13.1 | 27111701 |

technical change and errors excepted