

Product information

98 37 10

- For metric and imperial hexagonal head screws
- Basic tool chrome-plated
- Chrome Vanadium steel

Hexagon Socket for hexagonal screws

With internal square 3/8"

IEC 60900 DIN EN 60900



⚡ 1000 V ⚡

General

Article No.	98 37 10
EAN	4003773020578
Weight	32 g
Dimensions	42 x 23 x 23 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Width across flats S	10 mm
Ø of effective tool side d max.	18.7 mm
Square drive	3/8 Inch





Classification	
eCl@ss 5.1.4	21040218
ETIM 5.0	EC002203
ETIM 6.0	EC002203
proficl@ss 6.0	AAA805c006
UNSPSC 13.1	27111700

technical change and errors excepted