

Product information

98 55

Stripping Knives

With guide shoe

IEC 60900 DIN EN 60900

- Solid, fixed hook blade, sickle shaped
- With guide shoe at the blade point
- No damage of the conductor insulation
- Blade: surgical steel, stainless, vacuum-hardened
- Ergonomically designed handle shape with comfortable slip guard
- Particularly confident grip thanks to slip-proof soft components
- Thumb recess and "finger hook" at the end of the handle ensure a good transmission of force when the blade is pulled
- Transparent protective cap



⚡ 1000 V

General

Article No.	98 55
EAN	4003773022558
Handles	insulating multi-component handle, VDE-tested
Weight	77 g
Dimensions	180 x 46 x 26 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

Technical details

Blade length	38 mm
Radius	23.5 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040602
ETIM 5.0	EC000155
ETIM 6.0	EC000155
proficl@ss 6.0	EAB554c020
UNSPSC 13.1	23241609

Spare Parts

98 59 02	Spare Protecting Cap for 98 55,
----------	---------------------------------

technical change and errors excepted

