

KNIPEX Quality – Made in Germany



Rotatable  
grip inserts

15 adjustment  
positions for  
a clamping range  
of over 30 mm

For hoses with an  
outer diameter of  
up to 50 mm

## Spring Hose Clamp Pliers

Reliable gripping of clamps in any position

Now also available in 180 mm length

Handy, universal pliers for  
all standard clamps



Spring Hose Clamp Pliers

85  
51


Now also available in 180 mm length

► For confined spaces: the proven KNIPEX spring hose clamp pliers are now also available in a convenient length of 180 mm

- > Good accessibility due to compact design
- > Easy working: extremely good leverage of 5:1
- > Good access in any position due to rotatable grip inserts – also under load
- > Can be universally used for standard, space-saving, wire and special clamps with a nominal size of up to 50 mm
- > Over 30 mm clamping range; 15 adjusting positions
- > Damage-free gripping of hoses due to slight serration on the upper gripping jaw
- > Chrome vanadium electric steel, forged, oil-hardened



85 51 180 A



The practical rotatable grip inserts permit good accessibility to the clamp from any position

Product video



Space-saving clamp



Spring hose clamp




Spring band ring



Spring wire hose clamp



85 51 250 AF with locking device



85 51 250 A

Article No.	EAN 4003773-	↔ mm		Pliers	Handles	Adjustment positions	⚖ g	📦
85 51 180 A	081159	180		grey atramentized	with non-slip plastic coating	15	170	1
85 51 250 A	077329	250		grey atramentized	with non-slip plastic coating	25	340	1
85 51 250 AF	078632	250		grey atramentized	with non-slip plastic coating	19	350	1